

2-Port USB/VGA Cable KVM Switch with Cables and USB Peripheral Sharing

MODEL NUMBER: B032-VU2



Control 2 computers using one VGA monitor, USB keyboard and USB mouse. Connect a USB 1.1 hub (sold separately) to share USB peripherals, such as printers and hard drives, between computers.

Features

Access and Control 2 Computers with One Keyboard/Mouse/Monitor

- Recommended for home, office and multimedia applications
- Switch between computers using built-in remote port selector
- Supports video resolutions up to 2048 x 1536
- Built-in 3 ft. VGA and USB cables

Independent USB 1.1 Peripheral Sharing

- Adding an optional USB hub (sold separately) to the USB console mouse port allows connection of peripherals, such as printers, hard drives, scanners, webcams and thumb drives

Easy Plug-and-Play Setup and Use

- Compatible with Windows, Mac, Sun and Linux
- No external power supply, software or drivers to install
- Supports most mouse drivers and multifunction mice
- Takes up no valuable desk space

Specifications

OVERVIEW	
UPC Code	037332200389
Max CPU	2
Technology	VGA/SVGA

Highlights

- Built-in 3-ft. (0.91 m) VGA and USB cables
- Supports video resolutions up to 2048 x 1536
- Supports most mouse drivers and multifunction mice
- Easy remote port switching through built-in selector
- Compatible with Windows®, Mac®, Sun and Linux®

System Requirements

- VGA, SVGA or Multisync monitor
- USB keyboard
- USB mouse
- Computers with VGA and USB ports

Package Includes

- B032-VU2 2-Port USB/VGA Cable KVM Switch
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

VIDEO	
Number of Monitors Supported	1
Max Supported Video Resolution	2048 x 1536; DDC2B
Max Number of Ports (Entire Chain)	2
Extended Mode	No
Mirror Mode	No
CONNECTIONS	
Number of Ports	2
Daisy-Chain Port	No
Firmware Upgrade Port	No
PC/Server Connections	USB; VGA
Side A - Connector 1	HD15 (FEMALE)
Side A - Connector 2	(2) USB A (FEMALE)
Side B - Connector 1	(2) HD15 (MALE)
Side B - Connector 2	(4) USB A (MALE)
PHYSICAL	
Material of Construction	Plastic
Rackmountable	No
Shipping Dimensions (hwd / in.)	2.40 x 6.60 x 9.50
Shipping Dimensions (hwd / cm)	6.10 x 16.76 x 24.13
Shipping Weight (lbs.)	0.90
Shipping Weight (kg)	0.41
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Dimensions (hwd / cm)	2.59 x 7.9 x 6.6
Unit Weight (lbs.)	0.67
Unit Weight (kg)	0.30
ENVIRONMENTAL	
Operating Temperature Range	32° to 122°F (0° to 50°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Relative Humidity	0% to 80% RH, Non-Condensing
Operating Temperature	32° to 122°F (0° to 50°C)
COMMUNICATIONS	
Hotkey	No

Port Control	Push Buttons
IP Remote Access	No
FEATURES & SPECIFICATIONS	
NIAP-Certified Secure	No
Number of Users	1
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.