

2-Port USB/VGA Cable KVM Switch with Audio, Cables and USB Peripheral Sharing

MODEL NUMBER: **B032-VUA2**



Control 2 computers using one VGA monitor, USB keyboard and USB mouse. Connect a USB hub (sold separately) to share USB peripherals, such as printers and hard drives, between computers.

Features

Access and Control 2 Computers with One Keyboard/Mouse/Monitor

- Recommended for home, office, gaming and multimedia applications
- Switch between computers using hotkeys or mouse wheel
- Supports video resolutions up to 2048 x 1536
- Compliant with EDID
- Built-in 4-ft. (1.22 m) VGA, USB and audio cables and 3.5 mm speaker jack

Independent USB Peripheral Sharing

- Adding an optional USB hub (sold separately) to the USB console mouse port allows connection of peripherals, such as printers, hard drives, scanners, webcams and thumb drives

Flexible Keyboard/Mouse Applications

- Console mouse port emulation/bypass supports most mouse drivers and multifunction mice
- Works with gaming keyboards and wireless keyboards and mice
- Supports Mac and Sun keyboard emulation

Easy Plug-and-Play Setup and Use

- Compatible with Windows, Mac, Sun and Linux
- Plug and play—no software, drivers or external power required

Specifications

Highlights

- Built-in 4-ft. (1.22 m) VGA, USB and audio cables and 3.5 mm speaker jack
- Supports video resolutions up to 2048 x 1536
- Hotkey and mouse port switching
- Compatible with Windows®, Mac®, Sun and Linux®
- Plug and play—no software, drivers or external power required

System Requirements

- VGA, SVGA or multisync monitor
- USB keyboard
- USB mouse
- Speakers with 3.5 mm audio jack
- Computers with VGA and USB ports

Package Includes

- B032-VUA2 2-Port USB/VGA Cable KVM Switch
- Owner's manual



OVERVIEW	
UPC Code	037332200372
Technology	Stereo Audio; USB; VGA/SVGA
VIDEO	
Max Supported Video Resolution	2048 x 1536
INPUT	
Built-In Cable Length (ft.)	4
Built-In Cable Length (m)	1.2
Built-In Cable Length (in.)	48
Built-In Cable Length (cm)	121.9
Bus Powered	Yes
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	(x2) Port Selected (Green)
PHYSICAL	
Color	Black
Material of Construction	Plastic
Rackmountable	No
Shipping Dimensions (hwd / cm)	5.89 x 23.90 x 17.50
Shipping Dimensions (hwd / in.)	2.32 x 9.41 x 6.89
Shipping Weight (kg)	0.31
Shipping Weight (lbs.)	0.68
Unit Dimensions (hwd / cm)	2.6 x 6.6 x 7.9
Unit Dimensions (hwd / in.)	1 x 2.6 x 3.1
Unit Weight (kg)	0.32
Unit Weight (lbs.)	0.7
ENVIRONMENTAL	
Operating Temperature Range	32 to 122 F (0 to 50 C)
Storage Temperature Range	-4 to 140 F (-20 to 60 C)
Relative Humidity	0 to 80% RH, Non-Condensing
Power Consumption (Watts)	0.33
COMMUNICATIONS	



IP Remote Access	No
CONNECTIONS	
Ports	2
PC/Server Connections	USB; VGA
Side A - Connector 1	HD15 (FEMALE)
Side A - Connector 2	(2) USB A (FEMALE)
Side A - Connector 3	3.5MM (FEMALE)
Side B - Connector 1	(2) HD15 (MALE)
Side B - Connector 2	(2) USB A (MALE)
Side B - Connector 3	(2) 3.5MM (MALE)
Computer Keyboard and Mouse Interface	USB
Computer Monitor Interface	VGA
Console Keyboard and Mouse Interface	USB
Console Monitor Interface	VGA
FEATURES & SPECIFICATIONS	
Number of Users	1
NIAP-Certified Secure	No
Port Selection	Hotkey; Mouse
USB Hub Ports	Yes
Number of USB Hub Ports	1
USB Specification	USB 1.1 (up to 12 Mbps)
Cat5 KVM Switch	No
STANDARDS & COMPLIANCE	
Certifications	EMI/EMC EN55024; FCC Part 15 Class B; AS/NZS CISPR22; ANSI C63.4
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>