

NetDirector 16-Port Cat5 Matrix KVM Switch 1U Rack-Mount 2-User

MODEL NUMBER: **B060-016-2**



Description

Tripp Lite's 2-User 16-port NetDirector® 1U Rackmount Matrix KVM Switch is the optimal solution for controlling multiple computers (combination of PS/2, USB or Sun) by two independent, simultaneous users. A single unit occupies a mere 1U of rack space, yet can control up to 16 directly connected computers. A maximum of 1,024 computers can be connected through a combination of daisy-chaining and cascading. RJ45 connections allow signals to travel up to 150 meters away (500 ft.) using ordinary Cat5 cable, while maintaining video resolution. Use either PS/2 or USB console equipment to connect to PS/2, USB or SUN Servers.

For Government purchasers, B060-016-2 is Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases. Constructed of heavy-duty steel housing.

Features

- Three Level password security: Super Administrator, Administrator, and Users
- Superior video quality - up to 1024 x 768 @ 60Hz at 500ft.
- Auto Signal Compensation (ASC) assures optimum video resolution for distances up to 500ft between the switch and the consoles or computers - no dip switch setting required
- PS/2 keyboard and mouse emulation - computers boot even when the console focus is elsewhere. Keep Alive feature ensures that the keyboard and mouse work properly even if the switch temporarily loses power
- Daisy chain up to 7 additional B060-016 KVM Switches
- No software required; convenient computer selection via intuitive hotkey combinations or On Screen Display (OSD) menus
- OSD port list automatically expands when stations are added - port names are automatically reconfigured when the station sequence is changed
- OSD screen automatically adjusts to resolution changes
- Hot pluggable; add or remove components without having to power off the switch
- USB and PS/2 Consoles can control any combination of USB, PS/2, or SUN computers
- LCD, VGA, SVGA, XGA, and MultiSync support; DDC2B
- Rackmount Hardware Included

Highlights

- Two consoles independently and simultaneously control up to 16 directly connected computers, or over 1,000 when additional KVMs are connected
- Multi-platform support: PC, Sun or Mac
- Rackmountable in a 1U design...Rackmount Hardware Included
- Inexpensive Cat5 cabling makes cable management a breeze; up to 500 ft. distance from console to switch and up to 500 ft. from switch to servers
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

- Console: The Tripp Lite B062-002-PS2 or B062-002-USB Console Interface Module must be used to connect a console (Keyboard, Monitor and Mouse) to the KVM switch
- Computers: The Tripp Lite B054-001-SUN Server Interface Module must be used to connect a computer/server to the KVM switch

Package Includes

- 1 - B060-016-2 KVM Switch
- 1 - Power Cord
- 1 - Daisy Chain Cable
- 1 - CD with Owner's Manual
- 1 set - Rackmount Hardware



Powering Business Worldwide



- Lifetime firmware upgrading via flash ROM
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases
- Constructed of heavy-duty steel housing

Specifications

OVERVIEW	
UPC Code	037332138750
Console	No
Max CPU	1024
Technology	Cat5/5e; PS/2; VGA/SVGA
CONNECTIONS	
Number of Ports	16
PC/Server Connections	VGA; USB; PS/2
PHYSICAL	
Color	Black
LCD Monitor (cm)	Not Applicable
LCD Monitor (in.)	Not Applicable
Shipping Dimensions (hwd / in.)	1.75 x 17.00 x 11.00
Shipping Dimensions (hwd / cm)	4.44 x 43.18 x 27.94
Shipping Weight (lbs.)	11.80
Shipping Weight (kg)	5.35
ENVIRONMENTAL	
BTUs	38.6 to 41.7
COMMUNICATIONS	
Port Control	Hotkeys, OSD
IP Remote Access	Yes
FEATURES & SPECIFICATIONS	
NIAP-Certified Secure	No
Number of Users	2
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty



Powering Business Worldwide



1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.