

# USB Console Interface Module for NetDirector Matrix KVM Switches

MODEL NUMBER: **B062-002-USB**



## Description

This USB Console Interface Module allows a user to access a B060-Series NetDirector® Matrix KVM Switch from as far away as 500 feet. The console (keyboard, monitor and mouse) is connected to the HD15 port and USB port on the unit. The B062-002-USB is then connected to a B060-Series NetDirector Matrix KVM Switch via ordinary Cat5e cable.

The unit also includes a 2-in-1 USB KVM Cable kit for connecting to a local computer/server. Simply use the switch on the front of the box to toggle between PC use and KVM switch use...no need to set up a separate console station.

## Features

- Access a B060-Series NetDirector Matrix KVM switch from up to 500 ft. away
- Built-in KVM Switch for additional PC/server control
- Connects to KVM switch via inexpensive Cat5e patch cables
- Compact, space saving design
- Compliant with the Federal Trade Agreement Act (TAA) for GSA Schedule purchases

## Highlights

- Needed to connect a console (USB Keyboard, USB Mouse and HD15 Monitor) to a B060-Series NetDirector Matrix KVM Switch via Cat5e cable
- Connect to KVM Switch from up to 500 ft. away
- Module features a built-in KVM Switch for additional PC/server control
- Small footprint design takes up very little space on the desktop
- Compliant with the Federal Trade Agreement Act (TAA) for GSA Schedule purchases

## System Requirements

- USB keyboard, USB mouse and monitor with a HD15 port
- A B060-Series NetDirector Matrix KVM Switch
- Cat5e/6 cable; up to 500ft

## Package Includes

- 1 USB Console Interface Module with Built-in KVM Switch
- External power supply with NEMA 1-15P Plug (Input: 100-240V, 0.8A, 27-34VA, 50/60Hz Output: DC 5V, 2.6A)
- 2-in-1 USB KVM Cable Kit

## Specifications

OVERVIEW	
UPC Code	037332133137
Accessory Type	Server Interface Unit
Technology	Cat5/5e; VGA/SVGA
Accessory Class	KVM Switch Accessories
INPUT	
AC Power Adapter Plug(s)	NEMA 5-15P North America



Powering Business Worldwide



AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.8A
AC Power Adapter Output Specs (V / A)	5V / 2.6A
AC Power Adapter Cord Length (ft.)	4
AC Power Adapter Cord Length (m)	1.2
<b>POWER</b>	
Power Source Type	AC Adapter
AC Adapter	Input: 100-240V, 0.8A, 27-34VA, 50/60Hz Output: DC 5V, 2.6A
<b>CONNECTIONS</b>	
Computer/Server Ports	1
Included KVM Cable (Equipment Side) - Connector 1	HD15 (Male)
Included KVM Cable (Equipment Side) - Connector 2	USB A (Male)
<b>PHYSICAL</b>	
Color	Black
Shipping Dimensions (hwd / in.)	8.50 x 3.70 x 10.60
Shipping Dimensions (hwd / cm)	21.59 x 9.40 x 26.92
Shipping Weight (lbs.)	2.30
Shipping Weight (kg)	1.04
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	Trade Agreements Act (TAA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.