

# NetCommander PS2 Server Interface Unit (SIU)

MODEL NUMBER: **B078-101-PS2**



## Features

- Needed to connect a PS/2 Server to a B070 / B072-Series NetCommander KVM switch via Cat5e cable
- Eliminates the need for thicker, heavier KVM cables
- Compact, lightweight design
- Plug and Play; no software required
- No power supply required
- Allows a Server/CPU to be located up to 100-ft. (30.5 m) away from the KVM switch
- To convert DisplayPort or HDMI computers to VGA, use Tripp Lite adapters P134-06N-VGA-V2 or P131-06N

## Highlights

- Needed to connect a PS/2 Server to a B070 / B072-Series NetCommander KVM switch via Cat5e cable
- Easy to install; no software needed
- No power supply needed
- Allows a recommended maximum distance of 100-ft. (30.5 m) from KVM to Server via Cat5e cable
- Compact and lightweight design

## System Requirements

- Server or CPU with a HD15 port and (2) PS/2 type connections
- A B070 / B072-Series NetCommander Cat5 KVM Switch
- Cat5e/6 cable; up to 100-ft. (30.5 m)
- To convert DisplayPort or HDMI computers to VGA, use Tripp Lite adapters P134-06N-VGA-V2 or P131-06N

## Package Includes

- (x1) B078-101-PS2 PS/2 Server Interface Unit (SIU)

# Specifications

OVERVIEW	
UPC Code	037332148438
Technology	Cat5/5e; PS/2; VGA/SVGA
INPUT	



Bus Powered	Yes
Product Length (ft.)	1.2
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	GREEN (RECEIVING POWER); ORANGE (SELECTED AS ACTIVE PORT)
<b>PHYSICAL</b>	
Color	Gray
Material of Construction	ABS
Shipping Dimensions (hwd / cm)	2.79 x 13.00 x 14.99
Shipping Dimensions (hwd / in.)	1.10 x 5.12 x 5.90
Shipping Weight (kg)	0.11
Shipping Weight (lbs.)	0.24
Unit Weight (kg)	0.10
Unit Weight (lbs.)	0.22
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4 to 158 F (-20 to 70 C)
Storage Temperature Range	-4 to 158 F (-20 to 70 C)
<b>CONNECTIONS</b>	
Side A - Connector 1	HD15 (MALE)
Side A - Connector 2	(2) MINI DIN-6 (FEMALE)
Side B - Connector 1	RJ45 (FEMALE)
Computer Keyboard and Mouse Interface	PS/2
Computer Monitor Interface	VGA
<b>FEATURES &amp; SPECIFICATIONS</b>	
Driver Required	No
Recommended Category Cable	N105 - SERIES CAT5E SHIELDED CABLES
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to EN55022/EN55024, CE, FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>