

# NetCommander USB Server Interface Unit (SIU) - Single

MODEL NUMBER: **B078-101-USB-1**



## Description

The Tripp Lite NetCommander USB Server Interface Unit (SIU) connects to the HD15 port and USB port on a computer/server, and converts them to a single RJ45 connector. Ordinary Cat5e patch cables can then be used to connect the server to the switch ports on a Tripp Lite B070 / B072-Series NetCommander Cat5 KVM switch. Use of Cat5e cables frees up space in the installation that would ordinarily be filled by traditional, thicker KVM cables. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

## Features

- Needed to connect a USB Server to a B070 / B072-Series NetCommander KVM switch via Cat5e cable
- Eliminates the need for thicker, heavier KVM cables
- Compact, lightweight design
- Plug and Play; no software required
- No power supply required
- Allows a Server/CPU to be located up to 100ft away from the KVM switch
- To convert DisplayPort or HDMI computers to VGA, use Tripp Lite adapters P134-06N-VGA-V2 or P131-06N
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule Purchases

## Highlights

- Needed to connect a USB Server to a B070 / B072-Series NetCommander KVM switch via Cat5e cable
- Easy to install; no software needed
- No power supply required
- Allows a recommended maximum distance of 100ft from KVM to computer/server via Cat5e cable
- Compact and lightweight design

## System Requirements

- Server or CPU with a HD15 port and a USB port
- A B070 / B072-Series NetCommander Cat5 KVM Switch
- Cat5e/6 cable; up to 100ft
- To convert DisplayPort or HDMI computers to VGA, use Tripp Lite adapters P134-06N-VGA-V2 or P131-06N

## Package Includes

- (x1) B078-101-USB-1 USB Server Interface Unit (SIU)

## Specifications

OVERVIEW	
UPC Code	037332178688



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

<b>INPUT</b>	
Bus Powered	Yes
Product Length (ft.)	1.3
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	GREEN (RECEIVING POWER); ORANGE (SELECTED AS ACTIVE PORT)
<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	1.50 x 4.90 x 5.80
Shipping Dimensions (hwd / cm)	3.81 x 12.45 x 14.73
Shipping Weight (lbs.)	0.20
Shipping Weight (kg)	0.09
Unit Weight (lbs.)	0.18
Unit Weight (kg)	0.08
Material of Construction	ABS
Color	Gray
<b>CONNECTIONS</b>	
Side A - Connector 1	HD15 (MALE)
Side A - Connector 2	USB A (MALE)
Side B - Connector 1	RJ45 (FEMALE)
Computer Keyboard and Mouse Interface	USB
Computer Monitor Interface	VGA
<b>FEATURES &amp; SPECIFICATIONS</b>	
Driver Required	No
Recommended Category Cable	N105 - SERIES CAT5E SHIELDED CABLES
Technology	Cat5/5e; USB; VGA/SVGA
<b>CERTIFICATIONS</b>	
Certifications	Tested to EN55022/EN55024, CE, FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>