

# NetCommander USB Server Interface Unit (SIU) - 8-Pack

MODEL NUMBER: **B078-101-USB-8**



## Features

- 8-Pack of B078-101-USB-1 Server Interface Units
- Needed to connect a USB Server to a B070 / B072-Series NetCommander KVM switch via Cat5e cable
- Eliminates the need for thicker, heavier KVM cables
- Compact, lightweight design
- Plug and Play; no software required
- No power supply required
- Allows a Server/CPU to be located up to 100-ft. (30.5 m) away from the KVM switch
- To convert DisplayPort or HDMI computers to VGA, use adapters P134-06N-VGA-V2 or P131-06N
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## Highlights

- 8-Pack of B078-101-USB-1 Server Interface Units
- Needed to connect a USB Server to a B070 / B072-Series NetCommander KVM switch via Cat5e cable
- Easy to install; no software needed
- No power supply required
- Allows a recommended maximum distance of 100-ft. (30.5 m) from KVM to computer/server via Cat5e cable
- Compact and lightweight design

## System Requirements

- Server or CPU with a HD15 port and a USB port
- A B070 / B072-Series NetCommander Cat5 KVM Switch
- Cat5e/6 cable; up to 100ft
- To convert DisplayPort or HDMI computers to VGA, use adapters P134-06N-VGA-V2 or P131-06N

## Package Includes

- (x8) B078-101-USB-1 USB Server Interface Units (SIU)

## Specifications

| OVERVIEW             |                        |
|----------------------|------------------------|
| UPC Code             | 037332182470           |
| Accessory Type       | Server Interface Unit  |
| Technology           | Cat5/5e; VGA/SVGA      |
| Accessory Class      | KVM Switch Accessories |
| INPUT                |                        |
| Bus Powered          | Yes                    |
| Product Length (ft.) | 1.3                    |
| CONNECTIONS          |                        |



Powering Business Worldwide



|  |   |
|--|---|
| Side A - Connector 1                         | HD15 (MALE)   |
| Side A - Connector 2                         | USB A (MALE)  |
| Side B - Connector 1                         | RJ45 (FEMALE)   |
| Computer Keyboard and Mouse Interface        | USB   |
| Computer Monitor Interface                   | VGA   |
| <b>USER INTERFACE, ALERTS &amp; CONTROLS</b> |   |
| LED Indicators                               | GREEN (RECEIVING POWER); ORANGE (SELECTED AS ACTIVE PORT) |
| <b>PHYSICAL</b>                              |   |
| Color  | Gray  |
| Material of Construction                     | ABS   |
| Shipping Dimensions (hwd / in.)              | 4.50 x 6.00 x 10.30                                       |
| Shipping Dimensions (hwd / cm)               | 11.43 x 15.24 x 26.16                                     |
| Shipping Weight (lbs.)                       | 2.20  |
| Shipping Weight (kg)                         | 1.00  |
| Unit Packaging Type                          | Box   |
| Unit Weight (lbs.)                           | 0.18  |
| Unit Weight (kg)                             | 0.08  |
| <b>FEATURES &amp; SPECIFICATIONS</b>         |   |
| IP68 Rated                                   | No  |
| IP20 Rated                                   | No  |
| Driver Required                              | No  |
| Recommended Category Cable                   | N105 - SERIES CAT5E SHIELDED CABLES                       |
| <b>STANDARDS &amp; COMPLIANCE</b>            |   |
| Product Certifications                       | EN 55022; EN 55024  |
| Product Compliance                           | RoHS; CE (Europe); REACH; FCC (USA)                       |
| <b>WARRANTY &amp; SUPPORT</b>                |   |
| Product Warranty Period (Worldwide)          | 3-year limited warranty                                   |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.