

HDMI Splitter, 2-Port

MODEL NUMBER: B118-302-R



Description

Tripp Lite's HDMI Splitter allows the digital signal from a Blu-Ray player or other HDMI device, to be displayed on multiple HDMI or DVI-D Single Link monitors. Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p. Up to 32 displays can be connected by cascading up to three levels of additional splitters. Locate a monitor up to 41 ft. (12.5 m.) from a HDMI source; up to 16 ft. (5 m.) between the source and the splitter; up to 25 ft. (7.62 m.) between the splitter and a monitor. Splitters can be located up to 100 ft. away from the source using a combination of Tripp Lite long length HDMI cables (P568-050, P568-100-HD) and a HDMI Signal Booster (B122-000-60 or B123-001-60). Includes mounting hardware that allows the unit to be wallmounted, rackmounted or pole mounted. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Features

- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p.
- HDCP compliant
- Supports 3D, Lip-Sync Pass Through, and CEC Pass Through
- Connects to both HDMI and DVI-D Single-Link displays
- Cascade up to three levels of splitters to support up to 32 displays
- Includes mounting hardware that allows the unit to be wallmounted, rackmounted, or pole mounted
- Locate a monitor up to 41 ft. (12.5 m.) from a HDMI source; up to 16 ft. (5 m.) between the source and the switch; up to 25 ft. (7.62 m.) between the switch and a monitor
- ATC certified
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW

Highlights

- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p
- HDCP compliant
- Connects to both HDMI and DVI-D Single-Link displays
- ATC certified
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

- TV's with an available HDMI port and a HDMI peripheral device (e.g. Blu-Ray player, DVR, etc.)
- The cable connecting the HDMI source to the splitter must be no longer than 16 ft. (5 m.), unless using a signal booster (B122-000-60 or B123-001-60)
- The cable connecting the splitter to a HDMI monitor must be no longer than 25 ft. (7.62 m.)

Package Includes

- B118-302-R 2-Port HDMI Splitter
- 1 ft. HDMI cable
- Mounting hardware
- External Power Supply (Input: 100-240V, 50/60Hz, 0.4A Output: 5V, 2A)
- Owner's Manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

UPC Code	037332144157
AC Adapter	Input: 100-240V, 50/60Hz, 0.4A; Output: 5V, 2A, 4.9ft
Technology	HDMI
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	5.40 x 18.42 x 16.51
Shipping Dimensions (hwd / in.)	2.12 x 7.25 x 6.50
Shipping Weight (kg)	0.45
Shipping Weight (lbs.)	1.00
CONNECTIONS	
Ports	2
Side A - Connector 1	HDMI (FEMALE)
Side B - Connector 1	(2) HDMI (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>