

## 2x2 HDMI Matrix Switch with Remote Control - 1080p @ 60 Hz (HDMI 2xF/2xF), TAA

MODEL NUMBER: B119-2X2



Connect 2 HDMI source devices to 2 HDMI displays and either share video on both or switch between them.

### Description

Tripp Lite's B119-2X2 is a 2x2 HDMI Matrix Switch that routes high definition video from any two HDMI sources to any two HDMI displays. It supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p @ 60Hz. The 2x2 Matrix eliminates the need to disconnect and reconnect HDMI sources. It works with any HDMI source that connects to an HDMI display, and each source is accessible at all times by any display by selecting it with an IR remote, or using the RS232 port to switch the unit. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

### Features

- Share multiple HDMI sources between multiple monitors ( 2 Input, 2 Output )
- Allows any input to be routed to any output; or the same input to be routed to multiple outputs
- Switch between inputs via pushbuttons, remote control, or RS-232 serial
- Monitors can be located up to 25 ft. from the switch
- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p @ 60Hz
- HDCP and EDID compatible
- Mounting hardware included
- Plug-and-play; No software or drivers required
- Compatible with all operating systems
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## Specifications

### Highlights

- Share multiple HDMI sources between multiple monitors
- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p @ 60Hz
- Plug-and-play; No software or drivers required
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### Package Includes

- B119-2X2 Local Transmitter Unit
- External Power Supply with NEMA 1-15P Plug(Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A)
- 3.5 mm to DB9 Adapter Cable
- Mounting Hardware
- Remote Control
- Owner's Manual



<b>OVERVIEW</b>	
UPC Code	037332180186
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A
Technology	HDMI; IR; Serial (RS232)
<b>PHYSICAL</b>	
Color	Black
Shipping Dimensions (hwd / cm)	5.59 x 25.91 x 16.51
Shipping Dimensions (hwd / in.)	2.20 x 10.20 x 6.50
Shipping Weight (kg)	0.68
Shipping Weight (lbs.)	1.50
Unit Dimensions (hwd / cm)	3.05 x 23.37 x 9.91
Unit Dimensions (hwd / in.)	1.2 x 9.2 x 3.9
Unit Weight (kg)	0.66
Unit Weight (lbs.)	1.45
<b>COMMUNICATIONS</b>	
Port Control	Push Buttons
<b>CONNECTIONS</b>	
Ports	2
Side A - Connector 1	(2) HDMI (FEMALE)
Side B - Connector 1	(2) HDMI (FEMALE)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>