

4x4 HDMI Matrix Switch with Remote Control - 1080p @ 60 Hz (HDMI 4xF/4xF), TAA

MODEL NUMBER: B119-4X4



Connect 4 HDMI source devices to 4 HDMI displays and switch video signals between them.

Description

Tripp Lite B119-4X4 is a 4x4 HDMI Matrix Switch that routes high definition video from any four HDMI sources to any four HDMI displays. It supports video resolutions up to 1920 x 1200 (1080p) @ 60Hz. The 4x4 Matrix eliminates the need to disconnect and reconnect HDMI sources. It works with any HDMI source that connects to an HDMI display, and each source is accessible at all times by any display by selecting it with an IR remote, or using the RS232 port to switch the unit.

Features

- Share multiple HDMI sources between multiple monitors
- Allows any input to be routed to any output; or the same input to be routed to multiple outputs
- Switch between inputs via pushbuttons, remote control, or RS-232 serial
- Monitors can be located up to 25 ft. from the switch
- Supports video resolutions up to 1920 x 1200 (1080p) @ 60Hz
- HDCP and EDID compatible
- Mounting hardware included
- Plug-and-play; No software or drivers required
- Compatible with all operating systems
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

Highlights

- Share multiple HDMI sources between multiple monitors
- Supports video resolutions up to 1920 x 1200 (1080p) @ 60Hz
- Plug-and-play; No software or drivers required

Package Includes

- B119-4X4 Local Transmitter Unit
- External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 3A)
- 3.5 mm to DB9 Adapter Cable
- IR Extension Cable, 5 ft.
- Mounting Hardware
- Remote Control
- Owner's Manual



| OVERVIEW | |
|--------------------------------------|--|
| UPC Code | 037332180179 |
| AC Adapter | Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 3A |
| PHYSICAL | |
| Color | Black |
| Shipping Dimensions (hwd / cm) | 5.33 x 16.00 x 34.80 |
| Shipping Dimensions (hwd / in.) | 2.10 x 6.30 x 13.70 |
| Shipping Weight (kg) | 1.04 |
| Shipping Weight (lbs.) | 2.30 |
| Unit Dimensions (hwd / cm) | 3.05 x 23.37 x 9.91 |
| Unit Dimensions (hwd / in.) | 1.2 x 9.2 x 3.9 |
| Unit Weight (kg) | 0.66 |
| Unit Weight (lbs.) | 1.45 |
| COMMUNICATIONS | |
| Port Control | Push Buttons |
| CONNECTIONS | |
| Ports | 4 |
| Side A - Connector 1 | (4) HDMI (FEMALE) |
| Side B - Connector 1 | (4) HDMI (FEMALE) |
| FEATURES & SPECIFICATIONS | |
| Technology | HDMI; IR; Serial (RS232) |
| WARRANTY | |
| Product Warranty Period (Worldwide) | 3-year limited warranty |

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>