

HDMI over Dual Cat5/6 Extender Kit, In-Line Transmitter/Receiver for Video/Audio, IR, Up to 100 ft. (30.5 m), TAA

MODEL NUMBER: B125-101-60-IRU



Transmitter and receiver work in tandem to extend HDMI audio/video and IR control signals via Cat5/6 cable to a display up to 100 ft. Ideal for digital signs, schools, retail settings and trade show presentations.

Features

Extends HDMI Video/Audio and IR Control Signals to an HDMI Display

- Extends an HD 1920 x 1080 (1080p) signal up to 100-ft. (30.5 m) via 24 AWG solid-wire Cat5e/6 cable
- Ideal for digital signs, trade shows, presentations, classrooms, churches and retail settings
- Transmitter and receiver connect with dual Cat5e/6 cables (for best results, use Tripp Lite's N202-Series)
- Supports 7.1-channel surround sound, DTS-HD and Dolby TrueHD audio
- Supports EDID passthrough and HDCP
- IR remote control functionality lets you control Blu-ray player with its remote while standing at remote monitor

Easy to Set Up and Use

- Plug-and-play engineering—no software, drivers or external power supply
- Powered via included USB Micro-B cable
- Units connect quickly to source and display with HDMI cables (such as Tripp Lite's P568-Series)
- LEDs indicate when units are receiving power and a signal from the source
- Works with all operating systems and HDMI sources

TAA Compliant

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Highlights

- Supports high-definition video resolutions up to 1080p (@ 60 Hz)
- Supports 7.1-channel surround sound, DTS-HD and Dolby TrueHD
- Supports EDID passthrough, HDCP and 3D video
- USB Micro-B cable supplies power to either unit
- Plug and play—no software, drivers or external power supplies

System Requirements

- Computer, Blu-ray player or other source with HDMI port
- Display with HDMI port

NOTE

Package Includes

- Transmitter unit
- Receiver unit
- IR-TX cable, 5-ft. (1.52 m)
- IR-RX cable, 5-ft. (1.52 m)
- USB Micro-B cable, 3-ft. (0.91 m)
- Owner's manual



Specifications

OVERVIEW	
UPC Code	037332190468
Technology	HDMI; IR
VIDEO	
Max 1080P Range (ft)	100
Max 720P Range (ft)	100
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	19.99 x 14.20 x 4.39
Shipping Dimensions (hwd / in.)	7.87 x 5.59 x 1.73
Shipping Weight (kg)	0.28
Shipping Weight (lbs.)	0.62
COMMUNICATIONS	
Max 1024 x 768 Range (ft)	100
Max 480P Range (ft)	100
Max 1440 x 900 Range (ft)	100
Max 1080i Range (ft)	100
Max 480i Range (ft)	100
Max 640 x 480 Range (ft)	100
Max 800 x 600 Range (ft)	100
Max 1600 x 1200 Range (ft)	100
CONNECTIONS	
Ports	1
Side A - Connector 1	HDMI (FEMALE)
Side A - Connector 2	(2) RJ45 (FEMALE)
Side A - Connector 3	USB A (MALE)
Side B - Connector 1	HDMI (FEMALE)
Side B - Connector 2	(2) RJ45 (FEMALE)
WARRANTY	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (Worldwide)	1-year limited warranty
--	-------------------------

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>