

VGA over Cat5 Extender Kit (Transmitter + Receiver)

MODEL NUMBER: **B130-101**



Description

Tripp Lite's B130-101 allows you to extend a 1920 x 1440 (60Hz) video signal up to 500 ft., or a 1024 x 768 (60Hz) video signal up to 1,000 ft., when using 24Awg, Solid Wire Cat5e/6 cable, such as Tripp Lite's N022-01K-GY (Cat5) and N222-01K-GY (Cat6). For optimal image quality between 500 and 1,000 ft., use Zero-Skew cable, such as Tripp Lite P524-01K. The remote (Receiver) unit features built-in Equalization and Gain controls to adjust the video image. Includes mounting hardware for both local and remote units, allowing them to be wallmounted, rackmounted or pole mounted. Ideal for digital signage situations, such as retail, schools, churches, etc.

Features

- Extends a 1920 x 1440 (60Hz) video signal up to 500 ft., or a 1024 x 768 (60Hz) video signal up to 1,000 ft., when using 24Awg, Solid Wire Cat5e/6 cable, such as Tripp Lite's N022-01K-GY (Cat5) and N222-01K-GY (Cat6)
- For optimal image quality between 500 and 1,000 ft., use Zero-Skew cable, such as Tripp Lite P524-01K
- The remote (Receiver) unit features built-in Equalization and Gain controls to adjust the video image
- Includes mounting hardware for both local and remote units, allowing them to be wallmounted, rackmounted or pole mounted
- Ideal for digital signage situations, such as retail, schools, churches, etc.
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Highlights

- Extends a 1920 x 1440 (60Hz) video signal up to 500 ft., or a 1024 x 768 (60Hz) video signal up to 1,000 ft., when using 24Awg, Solid Wire Cat5e/6 cable, such as Tripp Lite's N022-01K-GY (Cat5) and N222-01K-GY (Cat6)
- For optimal image quality between 500 and 1,000 ft., use Zero-Skew cable, such as Tripp Lite P524-01K
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- Local (Transmitter) unit 1 x 4.5 x 2.5 (in.)
- Remote (Receiver) unit 1 x 2.5 x 3.5 (in.)
- Mini-Screwdriver for EQ/Gain adjustment
- (x2) Mounting Hardware Kits
- (x2) External Power Supply (Input: 100-240V, 50/60Hz, 0.5A Output: 5V, 2A)
- Owner's Manual

Specifications

OVERVIEW	
UPC Code	037332147455
Product Type	Cat5/Cat6 Extender Kit

Technology	VGA/SVGA
POWER	
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	2.20 x 10.20 x 7.60
Shipping Dimensions (hwd / cm)	5.59 x 25.91 x 19.30
Shipping Weight (lbs.)	1.80
Shipping Weight (kg)	0.82
CONNECTIONS	
Number of Ports	1
Side A - Connector 1	(2) HD15 (FEMALE)
Side A - Connector 2	RJ45 (FEMALE)
Side B - Connector 1	HD15 (FEMALE)
Side B - Connector 2	RJ45 (FEMALE)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty