

VGA with Audio over Cat5/Cat6 Extender Kit, Transmitter & Receiver with EDID, 2 Local/2 Remote Displays, 1440x900, Up to 500 ft. (152 m)

MODEL NUMBER: B130-202A



Features

- Connect up to 4 monitors - 2 local and 2 remote
- 3.5mm Stereo audio support and extension
- Extends a 1440 x 900 @ 60Hz signal up to 165 ft. (50 m) from the source
- Extends a 1024 x 768 @ 60Hz signal up to 500 ft. (150 m) from the source
- EDID copy feature ensures optimal display compatibility
- Built-in equalization control allows for adjustment of the video image
- All operating systems are supported
- Plug-and-play; no software or drivers are required
- HDCP compliant

Specifications

OVERVIEW	
UPC Code	037332182647
Product Type	Splitter; Extender Kit
Technology	VGA/SVGA; Stereo Audio; Cat5/5e; Cat6
Host Connector	HD15 (FEMALE)
VIDEO	
Max Supported Video Resolution	1440 x 900 @ 60Hz
Max 720P Range (ft)	165
Max 1280 x 720 (720p) Range (ft)	165

Highlights

- Extends a VGA + Stereo Audio signal up to 500 ft.
- Connect up to four VGA monitors: 2 Local and 2 Remote
- EDID copy feature ensures optimal display compatibility

System Requirements

- PC with VGA video output and 3.5mm Stereo output
- Monitors with VGA input; speakers with 3.5mm Stereo input

Package Includes

- Transmitter Unit
- Receiver Unit
- (2) External Power Supplies with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.5A Output: 5V, 2A, 4.5 ft.)
- Screwdriver for equalization adjustment
- Owner's manual



Powering Business Worldwide



Transmitter Video Input	VGA
Transmitter - Number of Video Outputs	2
Transmitter - Local Display Output	VGA
Receiver/Transceiver Video Output	VGA
Receiver - Number of Video Outputs	2
Range Extension using other Tripp Lite product	1000 ft. @ 1024 x 768 (60Hz) 500 ft. @ 1920 x 1440 (60Hz)
Recommended Cabling	Solid Wire Cat6 Cables (Tripp Lite's N202-Series)
Other Tripp Lite product used to extend range	B132-110A
HDR Support	No
3D Video Supported	No
Maximum Signal Range (ft)	500
Maximum Signal Range (m)	152
Maximum Signal Range Details	500 ft @ 1024 x 768 (60Hz) 165 ft @ 1440 x 900 (60Hz)
AUDIO	
Audio Input	3.5mm
Audio Output	3.5mm
Audio Specification	Stereo Audio
INPUT	
AC Power Adapter Plug(s)	NEMA 1-15P North America
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.5A
AC Power Adapter Output Specs (V / A)	5V / 2A
AC Power Adapter Cord Length (ft.)	4.5
AC Power Adapter Cord Length (m)	1.38
Bus Powered	No
POWER	
Power Source Type	AC Adapter
AC Plug Type	NEMA 1-15P
Power Source	Transmitter and Receiver (Included)
Power Over Cable (PoC) Support	No
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A, 4.5 ft.
DC Barrel Plug	OD: 5.5 x 2.1 x 7.5mm, Positive Pin, Negative Sleeve



Powering Business Worldwide



CONNECTIONS	
Number of Ports	2
Side A - Connector 1	(3) HD15 (FEMALE)
Side A - Connector 2	RJ45 (FEMALE)
Side A - Connector 3	3.5MM (FEMALE)
Side B - Connector 1	(2) HD15 (FEMALE)
Side B - Connector 2	RJ45 (FEMALE)
Side B - Connector 3	3.5MM (FEMALE)
Input x Output	1 x 4
Daisy-chainable / Cascadable	No
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	TX & RX: Red (Power); EDID (Orange); RJ45: Green (Connection), Orange (Data Transmission)
PHYSICAL	
Color	Black
Cable Length (ft.)	0
Cable Length (m)	0.00
Included Mounting Accessories	Wallmount
Number of Displays	4
Optional Mounting Accessory Notes	Can DIN Mount using Tripp Lite Bracket B110-DIN-01
Form Factor/Mounting Options	Box; Wall-mount
Receiver Unit Dimensions (hwd / in.)	4.53 x 1.06 x 2.46
Receiver Unit Weight (lbs.)	0.5
Shipping Dimensions (hwd / in.)	2.20 x 6.20 x 8.40
Shipping Dimensions (hwd / cm)	5.59 x 15.75 x 21.34
Shipping Weight (lbs.)	1.70
Shipping Weight (kg)	0.77
Transmitter Unit Dimensions (hwd / in.)	4.53 x 1.06 x 2.46
Transmitter Unit Weight (lbs.)	0.5
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Dimensions (hwd / cm)	Transmitter: 2.69 x 11.43 x 6.2 Receiver: 2.69 x 11.43 x 6.2
Unit Packaging Type	Box
Housing	Metal
ENVIRONMENTAL	



Powering Business Worldwide



Operating Temperature Range	32° to 122°F (0° to 50°C)
Storage Temperature Range	-4° to 158°F (-20° to 70°C)
Relative Humidity	10% to 90% RH, Non-Condensing
COMMUNICATIONS	
Max 1024 x 768 Range (ft)	500
Max 480P Range (ft)	500
Max 1440 x 900 Range (ft)	165
Max 480i Range (ft)	500
Max 640 x 480 Range (ft)	500
Max 800 x 600 Range (ft)	500
EDID Compatible	Yes
IR Remote Extension Support	No
RS-232 Serial Extension Support	No
Consumer Electronics Control (CEC) Supported	No
USB Extension Support	No
FEATURES & SPECIFICATIONS	
10/100 Ethernet Extension Support	No
MST Support	No
Built-In Equalizer	Yes
Driver Required	No
STANDARDS & COMPLIANCE	
External Power Supply Certifications	FCC; PSE; TUV; UL; cUL
Product Compliance	RoHS; REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
 Eaton is a registered trademark. All other trademarks
 are the property of their respective owners.