

VGA over Cat5 Extender 4-Port Transmitter

MODEL NUMBER: B132-004



Description

Tripp Lite's B132-004 takes a single VGA signal and splits it into 5 (1 local, 4 remote). When used in conjunction with a B132-100 or B132-100A remote unit, you can transmit a VGA signal from any VGA source to up to four displays over a single Cat5, Cat5e or Cat6 cable. A 1024 x 768 (60Hz) signal can be extended up to 500 ft. using 24Awg, Solid Wire UTP cable (Tripp Lite N202-Series). The number of displays can be increased to up to 13 (1 local, 12 remote) by daisy chaining up to 3 B132-004 units together. Up to 3 B132-004 units can be mounted in 1U of rack space using a Tripp Lite B132-004-RB Extender/Splitter 19 in. rackmount bracket. Video resolutions up to 1920x1440 @ 60Hz are supported. Remote units feature Equalization and Gain adjustment for crystal clear video. 1 year limited warranty.

Features

- Splits a single VGA signal into 5 (1 local, 4 remote)
- Extends a 1024 x 768 (60Hz) signal up to 500 ft. using 24Awg, Solid Wire UTP cable (Tripp Lite N202-Series)
- Expand the number of connected monitors to up to 13 (1 local, 12 remote) by daisy chaining up to 3 B132-004 Extender/Splitters together
- Up to 3 B132-004 units can be mounted in 1U of rack space using a Tripp Lite B132-004-RB Extender/Splitter 19 in. rackmount bracket
- Features an HD15 port for local monitor connection
- Compatible with VGA, SVGA, XGA, SXGA and UXGA computer resolutions
- Supports video resolutions up to 1920 x 1440 @ 60Hz
- Compatible with all operating systems
- 1 Year Ltd Warranty

Highlights

- Splits a single VGA signal into 5 (1 local, 4 remote)
- Extends a 1024 x 768 (60Hz) signal up to 500 ft. using 24Awg, Solid Wire UTP cable (Tripp Lite N202-Series)
- Compatible with VGA, SVGA, XGA, SXGA and UXGA computer resolutions
- Supports video resolutions up to 1920 x 1440 @ 60Hz

Package Includes

- B132-004 VGA Over Cat5 Extender/Splitter Local Unit
- 1 ft. VGA Daisychain Cable
- External Power Supply (Input: 100-240V, 50/60Hz, 1.5A Output: 12.6V, 3A)
- Owner's Manual

Specifications

OVERVIEW	
UPC Code	037332148780
Product Type	Cat5/Cat6 Transmitter



Powering Business Worldwide



Technology	VGA/SVGA
POWER	
AC Adapter	Input: 100-240V, 50/60Hz, 1.5A; Output: 12.6V, 3A
CONNECTIONS	
Number of Ports	4
Side A - Connector 1	HD15 (FEMALE)
Side B - Connector 1	(4) RJ45 (FEMALE)
Side B - Connector 2	HD15 (FEMALE)
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	2.20 x 5.80 x 8.90
Shipping Dimensions (hwd / cm)	5.59 x 14.73 x 22.61
Shipping Weight (lbs.)	2.10
Shipping Weight (kg)	0.95
Unit Dimensions (hwd / in.)	1.200 x 5.000 x 3.900
Unit Dimensions (hwd / cm)	2.79 x 12.7 x 10.16
Unit Weight (lbs.)	0.9
Unit Weight (kg)	0.41
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.