

## 4-Port Component Video + Stereo Audio over Cat5/Cat6 Extender Splitter, Box-Style Transmitter, Up to 700 ft., TAA

MODEL NUMBER: **B136-004**



### Description

Tripp Lite's B136-004 takes a single Component Video and Stereo Audio signal and splits it to five (1 local, 4 remote). When used in conjunction with a B136-100 remote unit, you can transmit a Component Video (YPbPr) and Stereo Audio signal from any DVD player, PS3, or Cable/Satellite device to up to four displays over a single CAT5, CAT5E, or CAT6 cable. A 1080i (60Hz) Component Video and Stereo Audio signal can be extended up to 300 ft. when using 24Awg, Solid Wire UTP cable (Tripp Lite N202-Series); or, up to 400 ft. when using Zero-Skew UTP cable (Tripp Lite P524-01K). A 480p (60Hz) Component Video and Stereo Audio signal can be extended up to 500 ft. when using 24Awg, Solid Wire UTP cable (Tripp Lite N202-Series); or, up to 700 ft. when using Zero-Skew UTP cable (Tripp Lite P524-01K). The number of displays can be increased to up to 13 (1 local, 12 remote) by daisy chaining 3 B136-004 units together. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

### Features

- Splits a single Component Video and Stereo Audio signal into five (1 local, 4 remote)
- Features an extra set of Component Video and Stereo Audio connectors for an optional local display
- Works in conjunction with a B136-100 remote unit
- A 1080i (60Hz) Component Video and Stereo Audio signal can be extended up to 300 ft. when using 24Awg, Solid Wire UTP cable (Tripp Lite N202-Series); or, up to 400 ft. when using Zero-Skew UTP cable (Tripp Lite P524-01K)
- A 480p (60Hz) Component Video and Stereo Audio signal can be extended up to 500 ft. when using 24Awg, Solid Wire UTP cable (Tripp Lite N202-Series); or, up to 700 ft. when using Zero-Skew UTP cable (Tripp Lite P524-01K)
- Connect up to 13 displays (1 local, 12 remote) by cascading 3 B136-004 units together
- Includes a 1 ft. Component Video + Stereo Audio daisychain cable

### Highlights

- Splits a single Component Video and Stereo Audio signal into five (1 local, 4 remote)
- Extends a 1080i (60Hz) Component Video and Stereo Audio signal up to 300 ft. when using 24Awg, Solid Wire UTP cable (Tripp Lite N202-Series); or, up to 400 ft. when using Zero-Skew UTP cable (Tripp Lite P524-01K)
- Connect up to 13 displays (1 local, 12 remote) by daisy chaining 3 B136-004 units together
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### System Requirements

#### Package Includes

- B136-004 4-Port Component Video + Stereo Audio Extender/Splitter
- External Power Supply with NEMA 1-15P Plug ( Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A, 5 ft. )
- 1 ft. Component Video + Stereo Audio Source / Daisychain cable
- Owner's Manual



- Up to 3 B136-004 units can be mounted in 1U of rack space when using a B132-004-RB Extender/Splitter 19 in. rackmount bracket
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## Specifications

OVERVIEW	
UPC Code	037332155559
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A, 5 ft.
PHYSICAL	
Color	Black
Included Mounting Accessories	Yes
Optional Mounting Accessory Notes	Up to 3 B136-004 units can be mounted in 1U of rack space when using a <a href="http://www.tripplite.com/VGA-over-Cat5-Extender-4-Port-Transmitter-B132-004">B132-004</a> -RB Extender/Splitter 19 in. rackmount bracket
Shipping Dimensions (hwd / cm)	5.59 x 21.34 x 1.27
Shipping Dimensions (hwd / in.)	2.20 x 8.40 x 0.50
Shipping Weight (kg)	0.86
Shipping Weight (lbs.)	1.90
Unit Dimensions (hwd / cm)	2.79 x 12.7 x 10.16
Unit Dimensions (hwd / in.)	1.1 x 5 x 4
Unit Weight (kg)	0.50
Unit Weight (lbs.)	1.1
COMMUNICATIONS	
Max 1024 x 768 Range (ft)	700
Max 480P Range (ft)	700
Max 1440 x 900 Range (ft)	400
Max 1080i Range (ft)	400
Max 480i Range (ft)	700
Max 640 x 480 Range (ft)	700
Max 800 x 600 Range (ft)	700
Max 1600 x 1200 Range (ft)	400
Max 720P Range (ft)	400
CONNECTIONS	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Ports	4
Side A - Connector 1	(5) RCA (FEMALE)
Side A - Connector 2	(5) RCA (FEMALE)
Side B - Connector 1	(4) RJ45 (FEMALE)
<b>FEATURES &amp; SPECIFICATIONS</b>	
Technology	Component; Stereo Audio
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>