

Component Video with Stereo Audio over Cat5/Cat6 Extender Kit, Wallplate Transmitter and Receiver, Up to 700 ft.

MODEL NUMBER: **B136-101-WP-1**



Is your TV or other display far away from your audio/video source? This wallplate kit allows a TV, projector, etc. with component video input to be placed up to 300 ft. away from a component audio/video source using ordinary Cat5e UTP cabling. It's great for presentation/conference rooms at a great price!

Description

Tripp Lite's B136-101-WP-1 Cat5 Extender Wallplate Kit with Component Video + Stereo Audio comes with both local and remote wallplates, allowing you to place a TV, Projector, etc up to 300 ft. away from the source. A 1080i (60Hz) Component Video and Stereo Audio signal can be extended up to 300 ft. when using 24Awg, Solid Wire UTP cable (Tripp Lite N022-01K-GY or N222-01K-GY); or up to 400 ft. when using Zero-Skew UTP cable (Tripp Lite P524-01K). A 480p (60Hz) Component Video and Stereo Audio signal can be extended up to 500 ft. when using 24Awg, Solid Wire UTP cable (Tripp Lite N022-01K-GY or N222-01K-GY); or up to 700 ft. when using Zero-Skew UTP cable (Tripp Lite P524-01K). Simple RJ45 Jack connection on the back of the wallplates. No external power required.

Features

- Comes with both local and remote wallplates
- Easy RJ45 rear connection jacks on both wallplates
- A 1080i (60Hz) Component Video and Stereo Audio signal can be extended up to 300 ft. when using 24Awg, Solid Wire UTP cable (Tripp Lite N022-01K-GY or N222-01K-GY); or, up to 400 ft. when using Zero-Skew UTP cable (Tripp Lite P524-01K)
- No external power required

Specifications

Highlights

- Extends a 1080i (60Hz) Component Video and Stereo Audio signal up to 300 ft.
- No external power required

Package Includes

- B136-101-WP-1 Cat5 Extender Wallplate Kit with Component Video + Stereo Audio (2 pieces)
- Wallplate Mounting Screws
- Owner's Manual



OVERVIEW	
UPC Code	037332162878
PHYSICAL	
Color	White
Shipping Dimensions (hwd / cm)	4.32 x 20.07 x 13.97
Shipping Dimensions (hwd / in.)	1.70 x 7.90 x 5.50
Shipping Weight (kg)	0.32
Shipping Weight (lbs.)	0.70
COMMUNICATIONS	
Max 1024 x 768 Range (ft)	700
Max 480P Range (ft)	700
Max 1440 x 900 Range (ft)	400
Max 1080i Range (ft)	400
Max 480i Range (ft)	700
Max 640 x 480 Range (ft)	700
Max 800 x 600 Range (ft)	700
Max 1600 x 1200 Range (ft)	400
Max 720P Range (ft)	400
CONNECTIONS	
Ports	1
Side A - Connector 1	(5) RCA (FEMALE)
Side A - Connector 2	RJ45 (FEMALE)
Side B - Connector 1	(5) RCA (FEMALE)
Side B - Connector 2	RJ45 (FEMALE)
FEATURES & SPECIFICATIONS	
Technology	Component; Stereo Audio
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

<https://www.tripplite.com/products/product-certification-agencies>