

## 12V DC, 54-Amp Replacement Battery for HCRK-54 Medical-Grade Mobile Power Retrofit Kit

MODEL NUMBER: **BP12V54**



### Highlights

- 12V DC, 54-Amp Replacement Battery for HCRK-54 Medical-Grade Mobile Power Retrofit Kit
- Sealed, Maintenance-Free

### Package Includes

- BP12V54 12V DC Battery
- Connection cable

### Description

12V DC, 54-Amp Replacement Battery for HCRK-54 Medical-Grade Mobile Power Retrofit Kit. Sealed lead acid, maintenance-free, spill/leak proof, AGM battery, simple plug-in connection with included cable – Included in the HCRK-54. This is the replacement battery for the HCRK-54 battery.

### Features

- 12V DC
- 54-Amp
- Simple plug-in connection with included cable
- Sealed, maintenance-free

## Specifications

OVERVIEW	
UPC Code	037332142450
INPUT	
Voltage Compatibility (VDC)	12
PHYSICAL	
Shipping Dimensions (hwd / cm)	24.64 x 31.75 x 29.72
Shipping Dimensions (hwd / in.)	9.70 x 12.50 x 11.70
Shipping Weight (kg)	21.52
Shipping Weight (lbs.)	47.44



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Unit Dimensions (hwd / cm)	16.51 x 22.23 x 25.4
Unit Dimensions (hwd / in.)	6.500 x 8.750 x 10.000
Unit Weight (kg)	19.96
Unit Weight (lbs.)	44
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	6-month limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>