

12V DC, 90-Amp Replacement Battery for HCRK and HCRK-INT Medical-Grade Mobile Power Retrofit Kits

MODEL NUMBER: **BP12V82**



Highlights

- 12V DC, 90-Amp Replacement Battery for HCRK and HCRK-INT Medical-Grade Mobile Power Retrofit Kits
- Sealed, Maintenance-Free

Package Includes

- BP12V82 12V DC Battery
- Connection cable

Description

12V DC, 90-Amp Replacement Battery for HCRK and HCRK-INT Medical-Grade Mobile Power Retrofit Kits. Sealed lead acid, maintenance-free, spill/leak proof, AGM battery, simple plug-in connection with included cable – Included in the HCRK and HCRK-INT. This is the replacement battery for the HCRK and HCRK-INT battery.

Features

- 12V DC
- 90-Amp
- Simple plug-in connection with included cable
- Sealed, maintenance-free

Specifications

OVERVIEW	
UPC Code	037332134042
INPUT	
Voltage Compatibility (VDC)	12
PHYSICAL	
Shipping Dimensions (hwd / cm)	33.78 x 37.59 x 53.85
Shipping Dimensions (hwd / in.)	13.30 x 14.80 x 21.20



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Weight (kg)	33.11
Shipping Weight (lbs.)	73.00
Unit Dimensions (hwd / cm)	17.78 x 21.59 x 36.83
Unit Dimensions (hwd / in.)	7.000 x 8.500 x 14.500
Unit Weight (kg)	27.90
Unit Weight (lbs.)	61.5
WARRANTY	
Product Warranty Period (Worldwide)	6-month limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>