

## 192V External Battery Pack for Select UPS Systems, 3U Rack/Tower, TAA

MODEL NUMBER: BP192V12RT3US



External smart battery pack provides extended runtime for compatible Tripp Lite Unity Power Factor UPS systems.

### Features

**External Battery Pack Gives Your Compatible UPS System Extended Runtime**The BP192V12RT3US is compatible only with UPS systems that specify the use of this battery pack (see *System Requirements* below). Not only does this external battery pack provide extended runtime, but it can also be daisy-chained using its input/output connectors to additional external battery packs for even longer extended-run operation. Heavy-gauge cabling with high-current DC connectors is included for simple installation.

**Smart Battery Communicates with Your UPS for Optimal Performance**This external battery pack with included power and data cabling is automatically sensed by the UPS for highly accurate runtime reporting and ideal charge current settings. An additional data cable reports battery pack temperature to the UPS to enable temperature-compensated charging to extend battery lifespan and fast recharge.

**Mounts in 3U of Space in 19 in. 4-Post Racks**This smart battery pack's multi-use form factor supports stacking or mounting in 3U of space in EIA-standard 19-inch racks using the included 4-post rack-mounting brackets. The four replaceable internal battery trays can be easily removed to make the battery pack lighter for rack-mount installation. The BP192V12RT3US is also compatible with 2-9U STAND for upright tower configuration and 2POSTRMKITHD for 2-post racks (both accessories sold separately).

### Highlights

- Connects to compatible 5kVA/6kVA Unity PF UPS systems for extended runtime
- Smart pack communicates with UPS to automatically report battery temperature, accurate runtime, etc.
- Daisy-chain connector supports additional battery packs for even longer runtime
- Mounts in 3U of space in 19 in. rack using included 4-post installation hardware
- Supports 2-post rack or tower installation with optional accessories (sold separately)

### Applications

- Extend the runtime of your compatible Tripp Lite UPS system
- Daisy-chain to additional battery packs to provide even longer extended-run operation

### System Requirements

5kVA and 6kVA SmartOnline Unity Power Factor UPS systems only: SU5KRT3UG, SU5KRT3UHV, SU5KRT3UHW, SU5KRT3UTF, SU5KRT3UX, SU6KRT3UG, SU6KRT3UHV, SU6KRT3UHW, SU6KRT3UTF, SU6KRT3UX, SU5KRT3UGMB, SU5KRT3UHVMB, SU5KRT3UHWMB, SU5KRT3UTFMB, SU6KRT3UGMB, SU6KRT3UHVMB, SU6KRT3UHWMB, SU6KRT3UTFMB, SU6KRT3UXMB and other UPS systems that specify the use of this battery pack

### Package Includes

- BP192V12RT3US 192V External Battery Pack, 3U Rack/Tower
- Smart battery communication cable
- 4-post rack-mounting hardware
- Owner's manual

## Specifications



Powering Business Worldwide

TRIPP LITE  
SERIES

OVERVIEW	
UPC Code	037332238610
INPUT	
Input Phase	Single-Phase
UPS Input Cord Length (ft.)	3
UPS Input Cord Length (m)	0.9
OUTPUT	
Overload Protection	50A DC output fuse
BATTERY	
Expandable Runtime	Yes
DC System Voltage (VDC)	192
UPS Connection	Detachable cable with UPS specific DC connector (90 cm length, 8 gauge)
Typical Battery Lifespan	4-6 years typical (North America)
PHYSICAL	
Material of Construction	Steel
Rack Height	3U
External Battery Pack Form Factor	Rack/Tower
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount ( <a href="//tripplite.eaton.com/2-Post-Rack-Mount-Installation-Kit-3U-Larger-UPS-Transformer-Battery-Pack-Components~2POSTRMKITHD">2-Post-Rack-Mount-Installation-Kit-3U-Larger-UPS-Transformer-Battery-Pack-Components~2POSTRMKITHD</a> ); Tower ( <a href="//tripplite.eaton.com/2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems~2-9USTAND">2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems~2-9USTAND</a> )
Minimum Required Rack Depth (cm)	78.74
Minimum Required Rack Depth (inches)	31
Shipping Dimensions (hwd / in.)	11.00 x 23.00 x 33.00
Shipping Weight (kg)	88.00
Unit Dimensions (hwd / in.)	5.250 x 17.500 x 28.000
Unit Dimensions (hwd / cm)	13,3 x 44,5 x 71,1
Unit Weight (lbs.)	174.00
Unit Weight (kg)	78.93
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA C22.2; CAN/CSA-C22.2 No. 107.3 (Canada); IEC/EN 62040; UL 1778
Product Compliance	RoHS; CE (Europe); Trade Agreements Act (TAA)



Powering Business Worldwide

TRIPP LITE  
SERIES

WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	2-year limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty
Optional Coverage	3 year, 5 year, next day and on-site warranty coverage available

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.