

## 192V External Battery Pack for Select Tripp Lite UPS Systems, 3U Rack/Tower

MODEL NUMBER: **BP192V12RT3US**



External smart battery pack provides extended runtime for compatible Tripp Lite Unity Power Factor UPS systems.

### Features

**External Battery Pack Gives Your Compatible Tripp Lite UPS System Extended Runtime**The BP192V12RT3US is compatible only with Tripp Lite UPS systems that specify the use of this battery pack (see *System Requirements* below). Not only does this external battery pack provide extended runtime, but it can also be daisy-chained using its input/output connectors to additional external battery packs for even longer extended-run operation. Heavy-gauge cabling with high-current DC connectors is included for simple installation.

**Smart Battery Communicates with Your UPS for Optimal Performance**This external battery pack with included power and data cabling is automatically sensed by the UPS for highly accurate runtime reporting and ideal charge current settings. An additional data cable reports battery pack temperature to the UPS to enable temperature-compensated charging to extend battery lifespan and fast recharge.

**Mounts in 3U of Space in 19 in. 4-Post Racks**This smart battery pack's multi-use form factor supports stacking or mounting in 3U of space in EIA-standard 19-inch racks using the included 4-post rack-mounting brackets. The four replaceable internal battery trays can be easily removed to make the battery pack lighter for rack-mount installation. The BP192V12RT3US is also compatible with Tripp Lite's 2-9U STAND for upright tower configuration and 2POSTRMKITHD for 2-post racks (both accessories sold separately).

### Highlights

- Connects to compatible Tripp Lite 5kVA/6kVA Unity PF UPS systems for extended runtime
- Smart pack communicates with UPS to automatically report battery temperature, accurate runtime, etc.
- Daisy-chain connector supports additional battery packs for even longer runtime
- Mounts in 3U of space in 19 in. rack using included 4-post installation hardware
- Supports 2-post rack or tower installation with optional accessories (sold separately)

### Applications

- Extend the runtime of your compatible Tripp Lite UPS system
- Daisy-chain to additional battery packs to provide even longer extended-run operation

### System Requirements

Tripp Lite 5kVA and 6kVA SmartOnline Unity Power Factor UPS systems only: SU5KRT3UG, SU5KRT3UHV, SU5KRT3UHW, SU5KRT3UTF, SU5KRT3UX, SU6KRT3UG, SU6KRT3UHV, SU6KRT3UHW, SU6KRT3UTF, SU6KRT3UX, SU5KRT3UGMB, SU5KRT3UHVMB, SU5KRT3UHWMB, SU5KRT3UTFMB, SU6KRT3UGMB, SU6KRT3UHVMB, SU6KRT3UHWMB, SU6KRT3UTFMB, SU6KRT3UXMB and other Tripp Lite UPS systems that specify the use of this battery pack



#### Package Includes

- BP192V12RT3US 192V External Battery Pack, 3U Rack/Tower
- Smart battery communication cable
- 4-post rack-mounting hardware
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332238610
INPUT	
UPS Input Cord Length (ft.)	3
UPS Input Cord Length (m)	0.9
Input Phase	Single-Phase
OUTPUT	
Overload Protection	50A DC output fuse
BATTERY	
Expandable Battery Runtime	Includes a second input/output connector to daisy-chain multiple battery packs
Expandable Runtime	Yes
DC System Voltage (VDC)	192
UPS Connection	Detachable cable with UPS specific DC connector (90 cm length, 8 gauge)
Typical Battery Lifespan	4-6 years typical (North America)
PHYSICAL	
External Battery Pack Form Factor	Rack/Tower
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount ( <a href="http://www.tripplite.com/2-Post-Rack-Mount-Installation-Kit-3U-Larger-UPS-Transformer-Battery-Pack-Components~2POSTRMKITHD">2-Post-Rack-Mount-Installation-Kit-3U-Larger-UPS-Transformer-Battery-Pack-Components~2POSTRMKITHD</a> ); Tower ( <a href="http://www.tripplite.com/2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems~2-9USTAND">2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems~2-9USTAND</a> )
Material of Construction	Steel
Minimum Required Rack Depth (cm)	91.44



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Minimum Required Rack Depth (inches)	36
Rack Height	3U
Shipping Dimensions (hwd / in.)	11.00 x 23.00 x 33.00
Shipping Weight (kg)	88.00
Unit Dimensions (hwd / cm)	13,3 x 44,5 x 71,1
Unit Dimensions (hwd / in.)	5.25 x 17.5 x 28
Unit Weight (kg)	78.93
Unit Weight (lbs.)	174.00
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to UL1778, TAA Compliant (USA), CAN/CSA (Canada), CE (International)
Certification Details	Series Number (s) AG-03F7; Safety Standards (Canada) CAN/CSA-C22.2 No. 107.3-14 (3rd Ed)+GI1; Safety Standards (International)IEC62040-1:2008 (1st Ed)+A1:2013
<b>WARRANTY</b>	
Product Warranty Period (U.S. & Canada)	2-year limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty
Optional Coverage	3 year, 5 year, next day and on-site warranty coverage available

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>