

192V External Battery Pack for Select UPS Systems, 3U Rack/Tower, TAA

MODEL NUMBER: **BP192V12RT3UTAA**



TAA-compliant external battery pack provides extended runtime for compatible 192V Tripp Lite UPS systems.

Features

Gives Your Compatible UPS System Extended RuntimeThe BP192V12RT3UTAA is compatible only with SU5000RT4UHVTA, SU6000RT4UHVTA and other UPS systems that specify the use of this battery pack. Not only does it provide extended runtime, but it can also be daisy-chained using its rear connector to additional external battery packs for even longer extended-run operation. Heavy-gauge cabling with high-current DC connectors is included for simple installation.

Mounts in 3U of Space in 19 in. 4-Post RacksThis battery pack's multi-use form factor supports stacking or mounting in 3U of space in EIA-standard 19-inch racks using the included 4-post rack-mounting brackets. The BP192V12RT3UTAA is also compatible with 2-9USTAND for upright tower configuration and 2POSTRMKITHD for 2-post racks (both accessories sold separately).

TAA-Compliant for GSA Schedule PurchasesThe BP192V12RT3UTAA is compliant with the Federal Trade Agreements Act for GSA Schedule purchases.

2-Year Warranty and Environmentally Responsible DesignThe BP192V12RT3UTAA comes with a 2-year warranty. It's manufactured in compliance with strict RoHS specifications.

Highlights

- Connects to expandable 192V DC UPS systems for extended runtime
- Daisy-chain connector supports additional battery packs for even longer runtime
- Mounts in 3U of space in 19 in. rack using included 4-post installation hardware
- Supports 2-post rack or tower installation with optional accessories (sold separately)
- Complies with Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Applications

- Extends the runtime of your compatible Tripp Lite UPS system
- Daisy-chains to additional battery packs to provide even longer extended-run operation

System Requirements

- SU5000RT4UHVTA or SU6000RT4UHVTA UPS system

Package Includes

- BP192V12RT3UTAA 192V External Battery Pack, 3U Rack/Tower, TAA
- Rack-mounting hardware
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332217806
INPUT	
Input Phase	Single-Phase
UPS Input Cord Length (ft.)	3
UPS Input Cord Length (m)	0.9

OUTPUT	
Overload Protection	50A DC output fuse
BATTERY	
Expandable Runtime	Yes
DC System Voltage (VDC)	192
UPS Connection	Detachable cable with UPS specific DC connector (90 cm length, 8 gauge)
Typical Battery Lifespan	4-6 years typical (North America)
PHYSICAL	
Material of Construction	Steel
Rack Height	3U
External Battery Pack Form Factor	Rack/Tower
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount (2-Post-Rack-Mount-Installation-Kit-3U-Larger-UPS-Transformer-Battery-Pack-Components~2POSTRMKITHD); Tower (2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems~2-9USTAND)
Minimum Required Rack Depth (cm)	78.74
Minimum Required Rack Depth (inches)	31
Shipping Dimensions (hwd / in.)	11.00 x 23.00 x 33.00
Shipping Dimensions (hwd / cm)	27.94 x 58.42 x 83.82
Shipping Weight (lbs.)	200.00
Shipping Weight (kg)	90.72
Unit Dimensions (hwd / in.)	5.250 x 17.500 x 28.000
Unit Dimensions (hwd / cm)	13.3 x 44.5 x 71.1
Unit Weight (lbs.)	174.00
Unit Weight (kg)	78.93
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	2-year limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty



Powering Business Worldwide



Product Warranty Period (Puerto Rico)	1-year limited warranty
Optional Coverage	3 year, 5 year, next day and on-site warranty coverage available

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.