

## 192V External Battery Pack for Select Tripp Lite UPS Systems, 3U Rack/Tower, TAA

MODEL NUMBER: **BP192V12RT3UTAA**



TAA-compliant external battery pack provides extended runtime for compatible 192V Tripp Lite UPS systems.

### Features

**Gives Your Compatible Tripp Lite UPS System Extended Runtime**The BP192V12RT3UTAA is compatible only with Tripp Lite's SU5000RT4UHVTA, SU6000RT4UHVTA and other UPS systems that specify the use of this battery pack. Not only does it provide extended runtime, but it can also be daisy-chained using its rear connector to additional external battery packs for even longer extended-run operation. Heavy-gauge cabling with high-current DC connectors is included for simple installation.

**Mounts in 3U of Space in 19 in. 4-Post Racks**This battery pack's multi-use form factor supports stacking or mounting in 3U of space in EIA-standard 19-inch racks using the included 4-post rack-mounting brackets. The BP192V12RT3UTAA is also compatible with Tripp Lite's 2-9U STAND for upright tower configuration and 2POSTRMKITHD for 2-post racks (both accessories sold separately).

**TAA-Compliant for GSA Schedule Purchases**The BP192V12RT3UTAA is compliant with the Federal Trade Agreements Act for GSA Schedule purchases.

**2-Year Warranty and Environmentally Responsible Design**The BP192V12RT3UTAA comes with a 2-year warranty. It's manufactured in compliance with strict RoHS specifications, reflecting Tripp Lite's commitment to environmental responsibility.

## Specifications

### Highlights

- Connects to expandable 192V DC Tripp Lite UPS systems for extended runtime
- Daisy-chain connector supports additional battery packs for even longer runtime
- Mounts in 3U of space in 19 in. rack using included 4-post installation hardware
- Supports 2-post rack or tower installation with optional accessories (sold separately)
- Complies with Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### Applications

- Extends the runtime of your compatible Tripp Lite UPS system
- Daisy-chains to additional battery packs to provide even longer extended-run operation

### System Requirements

- Tripp Lite SU5000RT4UHVTA or SU6000RT4UHVTA UPS system

### Package Includes

- BP192V12RT3UTAA 192V External Battery Pack, 3U Rack/Tower, TAA
- Rack-mounting hardware
- Owner's manual



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

<b>OVERVIEW</b>	
UPC Code	037332217806
<b>INPUT</b>	
UPS Input Cord Length (ft.)	3
UPS Input Cord Length (m)	0.9
Input Phase	Single-Phase
<b>OUTPUT</b>	
Overload Protection	50A DC output fuse
<b>BATTERY</b>	
Expandable Battery Runtime	Includes a second input/output connector to daisy-chain multiple battery packs
Expandable Runtime	Yes
DC System Voltage (VDC)	192
UPS Connection	Detachable cable with UPS specific DC connector (90 cm length, 8 gauge)
Typical Battery Lifespan	4-6 years typical (North America)
<b>PHYSICAL</b>	
External Battery Pack Form Factor	Rack/Tower
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount ( <a href="http://www.tripplite.com/2-Post-Rack-Mount-Installation-Kit-3U-Larger-UPS-Transformer-Battery-Pack-Components~2POSTRMKITHD">2-Post-Rack-Mount-Installation-Kit-3U-Larger-UPS-Transformer-Battery-Pack-Components~2POSTRMKITHD</a> ); Tower ( <a href="http://www.tripplite.com/2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems~2-9USTAND">2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems~2-9USTAND</a> )
Material of Construction	Steel
Minimum Required Rack Depth (cm)	91.44
Minimum Required Rack Depth (inches)	36
Rack Height	3U
Shipping Dimensions (hwd / cm)	27.94 x 58.42 x 83.82
Shipping Dimensions (hwd / in.)	11.00 x 23.00 x 33.00
Shipping Weight (kg)	90.72
Shipping Weight (lbs.)	200.00
Unit Dimensions (hwd / cm)	13.3 x 44.5 x 71.1
Unit Dimensions (hwd / in.)	5.25 x 17.5 x 28
Unit Weight (kg)	78.93
Unit Weight (lbs.)	174.00



<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	TAA Compliant
<b>WARRANTY</b>	
Product Warranty Period (U.S. & Canada)	2-year limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty
Optional Coverage	3 year, 5 year, next day and on-site warranty coverage available

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>