

## External 192V 4U Rack/Tower Battery Pack for select Tripp Lite UPS Systems (BP192V18-4U)

MODEL NUMBER: **BP192V18-4U**



### Highlights

- Extends runtime of compatible Tripp Lite UPS Systems with 192VDC external battery connection
- Provides daisy-chain capability
- Simple installation; 4U rackmount, tower or stack adaptable
- Simple maintenance chassis contains (4) 40lb. single-user replaceable battery modules

### Package Includes

- BP192V18-4U external battery pack
- Mounting Hardware
- Instruction manual with warranty information

### Description

Tripp Lite's BP192V18-4U rack/tower external battery pack offers extended battery runtime when used in conjunction with compatible Tripp Lite UPS systems. Multi-use form factor supports configuration in rackmount or stacking applications using only 4 rack spaces (4U). Upright tower configuration supported with optional 2-9USTAND accessory. Includes heavy-gauge cabling with high-current DC connectors for simple installation. Additional output connector allows multiple BP192V18-4U battery packs to be daisy-chained to the UPS for even longer extended run operation.

COMPATIBLE UPS SYSTEMS - SU12000RT4U, SU12000RT4UHW, SU16000RT4U, SU16000RT4UHW, and other Tripp Lite UPS systems that specify the use of this battery pack.

### Features

- Offers extended-run UPS operation when used in conjunction with compatible Tripp Lite UPS systems
- Supports stacking or rackmount installation using only 4 rack spaces (4U)
- Supports upright tower installation with optional 2-9USTAND accessory (holds 2 battery packs in tower configuration)
- Set of input/output connectors allows multiple BP192V18-4U battery packs to be daisy-chained to the UPS for even longer extended run operation
- Includes heavy-gauge cabling with high-current DC connectors for simple installation
- Simple maintenance chassis contains (4) 40lb. single-user replaceable battery modules

## Specifications

OVERVIEW	
UPC Code	037332139269
INPUT	
UPS Input Cord Length (ft.)	1.333

UPS Input Cord Length (m)	0.4
Input Phase	Single-Phase
<b>OUTPUT</b>	
Overload Protection	120A DC output fuse system
<b>BATTERY</b>	
Expandable Battery Runtime	Includes a second input/output connector to daisy-chain multiple BP192V18-4U battery packs
Expandable Runtime	Yes
DC System Voltage (VDC)	192
Battery Access	Front-panel battery access
Replacement Battery Cartridge	(2x) <a href="//www.tripplite.com/UPS-Replacement-192VDC-Battery-Cartridge-Kit-2-sets-of-8-for-select-Tripp-Lite-SmartOnline-UPS-RBC9-192">RBC9-192</a>
Battery Replacement Description	Simple maintenance chassis contains (4) 40lb. single-user replaceable sealed, flame retardant, non-spillable battery modules.
UPS Connection	Detachable cable with UPS specific DC connector (40.6 cm length, 4 gauge cable)
Typical Battery Lifespan	4-6 years typical (North America)
<b>PHYSICAL</b>	
Material of Construction	Steel
Rack Height	4U
External Battery Pack Form Factor	Rack/Tower
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount ( <a href="//www.tripplite.com/2-Post-Rack-Mount-Installation-Kit-3U-Larger-UPS-Transformer-Battery-Pack-Components-2POSTRMKITHD">2POSTRMKITHD</a> ); Tower ( <a href="//www.tripplite.com/2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems-2-9USTAND">2-9USTAND</a> )
Minimum Required Rack Depth (cm)	90.93
Minimum Required Rack Depth (inches)	35.8
Shipping Dimensions (hwd / in.)	13.00 x 33.00 x 23.00
Shipping Dimensions (hwd / cm)	33.02 x 83.82 x 58.42
Shipping Weight (lbs.)	284.00
Shipping Weight (kg)	128.82
Unit Dimensions (hwd / in.)	7.000 x 17.500 x 27.800
Unit Dimensions (hwd / cm)	18 x 44.5 x 70.6
Unit Weight (lbs.)	239
Unit Weight (kg)	108.41

STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe)
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	2-year limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty
Optional Coverage	3 year, 5 year, next day, on-site warranty coverage available