

## External 192V 4U Rack/Tower Battery Pack for select Tripp Lite UPS Systems (BP192V18-4U)

MODEL NUMBER: **BP192V18-4U**



### Description

Tripp Lite's BP192V18-4U rack/tower external battery pack offers extended battery runtime when used in conjunction with compatible Tripp Lite UPS systems. Multi-use form factor supports configuration in rackmount or stacking applications using only 4 rack spaces (4U). Upright tower configuration supported with optional 2-9USTAND accessory. Includes heavy-gauge cabling with high-current DC connectors for simple installation. Additional output connector allows multiple BP192V18-4U battery packs to be daisy-chained to the UPS for even longer extended run operation.

COMPATIBLE UPS SYSTEMS - SU12000RT4U, SU12000RT4UHW, SU16000RT4U, SU16000RT4UHW, and other Tripp Lite UPS systems that specify the use of this battery pack.

### Features

- Offers extended-run UPS operation when used in conjunction with compatible Tripp Lite UPS systems
- Supports stacking or rackmount installation using only 4 rack spaces (4U)
- Supports upright tower installation with optional 2-9USTAND accessory (holds 2 battery packs in tower configuration)
- Set of input/output connectors allows multiple BP192V18-4U battery packs to be daisy-chained to the UPS for even longer extended run operation
- Includes heavy-gauge cabling with high-current DC connectors for simple installation
- Simple maintenance chassis contains (4) 40lb. single-user replaceable battery modules

## Specifications

OVERVIEW	
UPC Code	037332139269
INPUT	

### Highlights

- Extends runtime of compatible Tripp Lite UPS Systems with 192VDC external battery connection
- Provides daisy-chain capability
- Simple installation; 4U rackmount, tower or stack adaptable
- Simple maintenance chassis contains (4) 40lb. single-user replaceable battery modules

### Package Includes

- BP192V18-4U external battery pack
- Mounting Hardware
- Instruction manual with warranty information



UPS Input Cord Length (ft.)	1.333
UPS Input Cord Length (m)	0.4
Input Phase	Single-Phase
<b>OUTPUT</b>	
Overload Protection	120A DC output fuse system
<b>BATTERY</b>	
Expandable Battery Runtime	Includes a second input/output connector to daisy-chain multiple BP192V18-4U battery packs
Expandable Runtime	Yes
DC System Voltage (VDC)	192
Battery Access	Front-panel battery access
Battery Replacement Description	Simple maintenance chassis contains (4) 40lb. single-user replaceable sealed, flame retardant, non-spillable battery modules.
UPS Connection	Detachable cable with UPS specific DC connector (40.6 cm length, 4 gauge cable)
Replacement Battery Cartridge	(2x) <a href="http://www.tripplite.com/UPS-Replacement-192VDC-Battery-Cartridge-Kit-2-sets-of-8-for-select-Tripp-Lite-SmartOnline-UPS-RBC9-192">RBC9-192</a>
Typical Battery Lifespan	4-6 years typical (North America)
<b>PHYSICAL</b>	
External Battery Pack Form Factor	Rack/Tower
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount ( <a href="http://www.tripplite.com/2-Post-Rack-Mount-Installation-Kit-3U-Larger-UPS-Transformer-Battery-Pack-Components-2POSTRMKITHD">2POSTRMKITHD</a> ); Tower ( <a href="http://www.tripplite.com/2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems-2-9USTAND">2-9USTAND</a> )
Material of Construction	Steel
Minimum Required Rack Depth (cm)	90.93
Minimum Required Rack Depth (inches)	35.8
Rack Height	4U
Shipping Dimensions (hwd / cm)	33.02 x 83.82 x 58.42
Shipping Dimensions (hwd / in.)	13.00 x 33.00 x 23.00
Shipping Weight (kg)	128.82
Shipping Weight (lbs.)	284.00
Unit Dimensions (hwd / cm)	18 x 44.5 x 70.6
Unit Dimensions (hwd / in.)	7 x 17.5 x 27.8
Unit Weight (kg)	108.41
Unit Weight (lbs.)	239



<b>WARRANTY</b>	
Product Warranty Period (U.S. & Canada)	2-year limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty
Optional Coverage	3 year, 5 year, next day, on-site warranty coverage available

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>