

External 192V 2U Rackmount Battery Pack for select Tripp Lite UPS Systems (BP192V5RT2U)

MODEL NUMBER: **BP192V5RT2U**



Highlights

- Extends the runtime of expandable 192V DC Tripp Lite UPS Systems
- Supports 2U rackmount installation; 4 post installation accessories included
- Options for 2 post rackmount available

Package Includes

- BP192V5RT2U external battery pack
- Mounting hardware
- Warranty information
- Instruction manual

Description

Tripp Lite's BP192V5RT2U rack external battery pack offers extended battery runtime when used in conjunction with compatible Tripp Lite UPS systems. Multi-use form factor supports configuration in rackmount or stacking applications using only 2 rack spaces (2U). Includes heavy-gauge cabling with high-current DC connectors for simple installation. COMPATIBLE UPS SYSTEMS - SU5000RT4U, SU6000RT4U, SU8000RT4U, SU5000RT4UHV, SU5000RT4UTF, SU6000RT4UHV, SU6000RT4UHVG, SU6000RT4UHVHW, SU6000RT4UHVPM, SU6000RT4UTFHW, SU6000RT4UTF and other Tripp Lite UPS systems that specify the use of this battery pack.

Features

- Offers extended-run UPS operation when used in conjunction with compatible Tripp Lite UPS systems
- Supports stacking or rackmount installation using only 2 rack spaces (2U)
- Mounting accessories included for 4 post rackmount installation
- Optional 2POSTRMKITWM enables installation in 2 post racks
- Includes heavy-gauge cabling with high-current DC connectors for simple installation
- COMPATIBLE UPS SYSTEMS - SU5000RT4U, SU6000RT4U, SU8000RT4U, SU5000RT4UHV, SU5000RT4UTF, SU6000RT4UHV, SU6000RT4UHVG, SU6000RT4UHVHW, SU6000RT4UHVPM, SU6000RT4UTFHW, SU6000RT4UTF and other Tripp Lite UPS systems that specify the use of this battery pack.
- NOTE: LIMIT OF 1 BP192V5RT2U PER UPS, SEE BP192V12-3U FOR MULTI-PACK COMPATIBILITY

Specifications

OVERVIEW



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

UPC Code	037332183781
INPUT	
UPS Input Cord Length (ft.)	3
UPS Input Cord Length (m)	0.9
Input Phase	Single-Phase
BATTERY	
Expandable Battery Runtime	Includes a second input/output connector to daisy-chain multiple battery packs
DC System Voltage (VDC)	192
UPS Connection	Detachable cable with UPS specific DC connector (90 cm length)
Typical Battery Lifespan	4-6 years typical (North America)
Expandable Runtime	Yes
PHYSICAL	
External Battery Pack Form Factor	Rack
Installation Form Factor Notes	Upright vertical tower configuration is not recommended for this model
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount (2POSTRMKITWM)
Material of Construction	Steel
Minimum Required Rack Depth (cm)	70.61
Minimum Required Rack Depth (inches)	27.8
Rack Height	2U
Shipping Dimensions (hwd / cm)	24.79 x 66.29 x 71.30
Shipping Dimensions (hwd / in.)	9.76 x 26.10 x 28.07
Shipping Weight (kg)	48.99
Shipping Weight (lbs.)	108.00
Unit Dimensions (hwd / cm)	8,7 x 44 x 50,4
Unit Dimensions (hwd / in.)	3.43 x 17.32 x 19.83
Unit Weight (kg)	34.11
Unit Weight (lbs.)	75.20
WARRANTY	
Product Warranty Period (U.S. & Canada)	2-year limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty
Optional Coverage	3 year, 5 year, next day and on-site warranty coverage available

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>