



External 192V 2U Rack-Mount Battery Pack for Select UPS Systems (BP192V5RT2U)

MODEL NUMBER: BP192V5RT2U





Highlights

- Extends the runtime of expandable 192V DC UPS Systems
- Supports 2U rack-mount installation; 4-post installation accessories included
- Options for 2-post rack-mount available

Package Includes

- BP192V5RT2U external battery pack
- Mounting hardware
- Warranty information
- Instruction manual

Description

The BP192V5RT2U rack external battery pack offers extended battery runtime when used in conjunction with compatible UPS systems. Multi-use form factor supports configuration in rack-mount or stacking applications using only two rack spaces (2U). Includes heavy-gauge cabling with high-current DC connectors for simple installation. COMPATIBLE UPS SYSTEMS include SU5000RT4U, SU6000RT4U, SU5000RT4UHV, SU5000RT4UHV, SU5000RT4UHV, SU6000RT4UHVG, SU6000RT4UHVHW, SU6000RT4UHVPM, SU6000RT4UTFHW, SU6000RT4UHVF and other UPS systems that specify the use of this battery pack.

Features

- · Offers extended-run UPS operation when used in conjunction with compatible UPS systems
- Supports stacking or rack-mount installation using only 2 rack spaces (2U)
- Mounting accessories included for 4-post rack-mount installation
- Optional 2POSTRMKITWM enables installation in 2-post racks
- Includes heavy-gauge cabling with high-current DC connectors for simple installation
- COMPATIBLE UPS SYSTEMS SU5000RT4U, SU6000RT4U, SU8000RT4U, SU5000RT4UHV, SU5000RT4UTF, SU6000RT4UHV, SU6000RT4UHVG, SU6000RT4UHVHW, SU6000RT4UHVPM, SU6000RT4UTFHW, SU6000RT4UTF and other UPS systems that specify the use of this battery pack.
- NOTE: LIMIT OF 1 BP192V5RT2U PER UPS, SEE BP192V12-3U FOR MULTI-PACK COMPATIBILITY

Specifications

OVERVIEW		
UPC Code	037332183781	
INPUT		
Input Phase	Single-Phase	
UPS Input Cord Length (ft.)	3	





UPS Input Cord Length (m)	0.9
BATTERY	
Expandable Runtime	Yes
DC System Voltage (VDC)	192
UPS Connection	Detachable cable with UPS specific DC connector (90 cm length)
Typical Battery Lifespan	4-6 years typical (North America)
PHYSICAL	
Material of Construction	Steel
Rack Height	2U
External Battery Pack Form Factor	Rack
Installation Form Factor Notes	Upright vertical tower configuration is not recommended for this model
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount (<a class="productLink" href="//tripplite.eaton.com/2-Post-Rack-Mount-Wall-Mount-
Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM">2POSTRMKITWM)
Minimum Required Rack Depth (cm)	58.42
Minimum Required Rack Depth (inches)	23
Shipping Dimensions (hwd / in.)	9.76 x 26.10 x 28.07
Shipping Dimensions (hwd / cm)	24.79 x 66.29 x 71.30
Shipping Weight (lbs.)	108.00
Shipping Weight (kg)	48.99
Unit Dimensions (hwd / in.)	3.430 x 17.320 x 19.830
Unit Dimensions (hwd / cm)	8,7 x 44 x 50,4
Unit Weight (lbs.)	75.20
Unit Weight (kg)	34.11
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe)
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	2-year limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty
Optional Coverage	3 year, 5 year, next day and on-site warranty coverage available





1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.