

## ±120VDC External Battery Cabinet for Select 10-60K S3M-Series 3-Phase UPS - Requires 20x 100Ah Batteries (Not Included)

MODEL NUMBER: BP240V100-NIB



External battery pack provides extended backup runtime for select Tripp Lite 10-60K S3M-Series 3-phase UPS systems.

### Features

#### ±120VDC Battery Cabinet Gives Your Compatible 3-Phase UPS Extended Runtime

This external battery pack connects to a compatible SmartOnline® S3M-Series 3-phase UPS system to provide long-lasting battery backup for data centers, telecommunications, networks, industrial facilities, security, emergency systems and other mission-critical applications that require high capacity, high availability and extended runtime. In addition to battery backup and extended runtime, the BP240V100-NIB can also be daisy-chained to other external battery cabinets for even longer extended-run operation.

#### Rugged Steel Construction Designed to Last in Demanding IT Applications

The cabinet is made from heavy-gauge steel with a baked powder-coated finish that helps prevent chipping and corrosion. The hinged front door provides easy access to the user-installed internal batteries. The door locks securely to help prevent damage, tampering or theft. Fuses and output breaker protect against potentially hazardous overcurrent.

#### Ships Ready for Immediate Battery Installation

All required internal battery cabling is included. External battery cables feed into the cabinet through conduit knockouts built into the bottom panel.

### Highlights

- Ideal for IT applications requiring high capacity, high availability and longer runtime
- Supports daisy-chaining to additional battery packs of same model for even more runtime
- Steel cabinet with locking door for easy access to user-installed VRLA (AGM) batteries
- Fuses and output breaker protect against potentially hazardous overcurrent
- Industrial design matches UPS cabinets for a clean, professional appearance

### Applications

- Extend the runtime of your compatible Tripp Lite UPS system to maintain operation during all power conditions
- Daisy-chain to additional battery cabinets to provide even longer extended-run operation for backing up essential equipment
- Customize your application with the internal batteries of your choice

### System Requirements

Tripp Lite 3-phase 208V UPS models S3M10K-NIB, S3M15K-NIB, S3M20K-NIB, S3M25K, S3M30K, S3M50K, S3M60K or other UPS specifying compatibility

### Package Includes

- BP240V100-NIB External Battery Cabinet for Select 10-60K S3M-Series 3-Phase UPS
- (2) External battery cables, 3 m



- (10) Internal battery cables
- (13) Copper jumper bars
- (4) Cabinet bottom side metal skirts
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332257802
INPUT	
Input Phase	3-Phase
BATTERY	
Expandable Battery Runtime	Multiple battery packs can be daisy-chained to the UPS for extended runtime
Expandable Runtime	Yes
DC System Voltage (VDC)	+/- 120VDC
UPS Connection	Hardwire (contractor supplies wiring - see Owner's Manual for gauge recommendations and complete installation instructions)
PHYSICAL	
External Battery Pack Form Factor	Tower
Material of Construction	Steel
Rack Height	0U
Shipping Dimensions (hwd / in.)	54.90 x 36.20 x 41.20
Shipping Weight (kg)	330.26
Unit Dimensions (hwd / cm)	119.89 x 80 x 89.92
Unit Dimensions (hwd / in.)	47.2 x 31.5 x 35.4
Unit Weight (kg)	260.23
Unit Weight (lbs.)	573.7
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>