

24V 2U External Rack/Tower Battery Pack for Select Tripp Lite UPS Systems (BP24V15RT2U)

MODEL NUMBER: **BP24V15RT2U**



Highlights

- Extends the runtime of expandable 24V DC Tripp Lite UPS Systems
- Included mounting accessories for 2U rack-mount installation in 2- or 4-post racks
- Tower support brackets included; options for wall-mount installation available
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- BP24V15RT2U external battery pack with attached DC cabling
- 2- and 4-post rack-mount/tower installation brackets
- Owner's manual

Description

BP24V15RT2U rack/tower external battery pack offers extended battery runtime when used in conjunction with expandable 24V Tripp Lite rack-mount and tower UPS systems. Includes heavy-gauge cabling with high-current DC connector for safe, simple installation. Included mounting accessories support 2U rack-mount installation in 2- or 4-post racks with additional support for upright tower placement. Wall-mount installation option available. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Compatible with these UPS systems: OMNIVS1500XL, OMNIVSINT1500XL, SMART1500LCDXL, SMART750RMXL2U, SMART750XLA, SU750RTLXL2U, SU750RTLXCD2U, SU750XL, SU1000RTLXL2UA, SU1000RTLXCD2U, SU1000XLA, SU1000XLCD, SUINT1000RTLXL2UA, and other Tripp Lite UPS systems that specify the use of this battery pack.

Features

- Offers extended-run UPS operation when used in conjunction with compatible 24V DC Tripp Lite UPS systems
- Includes heavy-gauge cabling with high-current DC connectors for simple installation
- Included mounting brackets support upright tower and 2U rack-mount installation in 2- or 4-post racks
- Included brackets also support upright tower installation
- 2POSTRMKITWM option enables wall-mount installation
- NOTE: LIMIT OF 1 BP24V15RT2U PER UPS, SEE BP24V70-3U or BP24V36-2US FOR MULTI-PACK COMPATIBILITY

Specifications

OVERVIEW	
UPC Code	037332141538
INPUT	

Input Phase	Single-Phase
BATTERY	
DC System Voltage (VDC)	24
UPS Connection	Attached 24VDC 75amp connector
PHYSICAL	
Rack Height	2U
External Battery Pack Form Factor	Rack/Tower
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount; 2 post 19 inch rackmount; Tower
Installation Form Factors Supported with Optional Accessories	Wallmount (2POSTRMKITWM)
Minimum Required Rack Depth (cm)	34.29
Minimum Required Rack Depth (inches)	13.5
Optional Mounting Accessory Notes	2POSTRMKITWM ; enables wall-mount installation
Shipping Dimensions (hwd / in.)	7.20 x 21.26 x 14.96
Shipping Dimensions (hwd / cm)	18.29 x 54.00 x 38.00
Shipping Weight (lbs.)	27.02
Shipping Weight (kg)	12.26
Unit Dimensions (hwd / in.)	3.500 x 17.330 x 10.680
Unit Dimensions (hwd / cm)	8,86 x 44,02 x 27,13
Unit Weight (lbs.)	24.31
Unit Weight (kg)	11.03
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	2-year limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty
Optional Coverage	Extended warranty options available



1000 Eaton Boulevard
Cleveland, OH 44122
United States



© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.