

External 24V 2U Rack/Tower Battery Pack for select Tripp Lite UPS Systems (BP24V15RT2U)

MODEL NUMBER: **BP24V15RT2U**



Description

BP24V15RT2U rack/tower external battery pack offers extended battery runtime when used in conjunction with expandable 24V Tripp Lite rackmount and tower UPS systems. Includes heavy gauge cabling with high current DC connector for safe, simple installation. Included mounting accessories support 2U rackmount installation in 2 or 4 post racks, with additional support for upright tower placement. Wallmount installation option available.

Compatible with these UPS Systems - OMNIVS1500XL, OMNIVSINT1500XL, SMART1500LCDXL, SMART750RMXL2U, SMART750XLA, SU750RTXL2U, SU750RTXLCD2U, SU750XL, SU1000RTXL2UA, SU1000RTXLCD2U, SU1000XLA, SU1000XLCD, SUINT1000RTXL2UA and other Tripp Lite UPS systems that specify the use of this battery pack.

Features

- Offers extended-run UPS operation when used in conjunction with compatible 24V DC Tripp Lite UPS systems
- Includes heavy gauge cabling with high current DC connectors for simple installation
- Included mounting brackets support upright tower and 2U rackmount installation in 2 or 4 post racks
- Included brackets also support upright tower installation
- 2POSTRMKITWM option enables wallmount installation
- NOTE: LIMIT OF 1 BP24V15RT2U PER UPS, SEE BP24V70-3U or BP24V36-2US FOR MULTI-PACK COMPATIBILITY

Specifications

Highlights

- Extends the runtime of expandable 24V DC Tripp Lite UPS Systems
- Included mounting accessories for 2U rackmount installation in 2 or 4 post racks
- Tower support brackets included; Options for wallmount installation available

Package Includes

- BP24V15RT2U External battery pack with attached DC cabling
- 2 and 4 post rackmount / tower installation brackets
- Owner's manual



OVERVIEW	
UPC Code	037332141538
INPUT	
Input Phase	Single-Phase
BATTERY	
DC System Voltage (VDC)	24
UPS Connection	Attached 24VDC 75amp connector
PHYSICAL	
External Battery Pack Form Factor	Rack/Tower
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount; 2 post 19 inch rackmount; Tower
Installation Form Factors Supported with Optional Accessories	Wallmount (2POSTRMKITWM)
Minimum Required Rack Depth (cm)	34.29
Minimum Required Rack Depth (inches)	13.5
Optional Mounting Accessory Notes	2POSTRMKITWM ; enables wall-mount installation
Rack Height	2U
Shipping Dimensions (hwd / cm)	18.29 x 54.00 x 38.00
Shipping Dimensions (hwd / in.)	7.20 x 21.26 x 14.96
Shipping Weight (kg)	12.26
Shipping Weight (lbs.)	27.02
Unit Dimensions (hwd / cm)	8,86 x 44,02 x 27,13
Unit Dimensions (hwd / in.)	3.49 x 17.33 x 10.68
Unit Weight (kg)	11.03
Unit Weight (lbs.)	24.31
STANDARDS & COMPLIANCE	
Certifications	CE; RoHS
WARRANTY	
Product Warranty Period (U.S. & Canada)	2-year limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (Puerto Rico)	1-year limited warranty
Optional Coverage	Extended warranty options available

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>