

External 24V 2U Rack-Mount Battery Pack for Select UPS Systems (BP24V28-2U)

MODEL NUMBER: BP24V28-2U



Highlights

- Extends the runtime of expandable 24V DC UPS Systems
- Supports 2U rack-mount installation; 4-post installation accessories included
- Options for 2-post rack-mount and wall-mount installation available

Package Includes

- BP24V28-2U external battery pack with attached DC cabling
- 4 post compatible rack mounting hardware
- 8 rubber feet for flat floor mounting
- Owner's manual

Description

BP24V28-2U rack-mount external battery pack offers extended battery runtime when used in conjunction with expandable 24V rack-mount UPS systems. Includes heavy-gauge cabling with high-current DC connector for safe, simple installation. Included mounting accessories support 2U rack-mount installation in 4-post racks. Options for 2-point front-rail mounting, 2-post center-mounting and wall-mount installation available.

Compatible with SMART750RML2U, SU750RTL2U, SU1000RTL2UA, SUINT1000RTL2UA and other UPS systems that specify the use of this battery pack.

Features

- Offers extended-run UPS operation when used in conjunction with compatible 24V DC UPS systems
- Includes heavy-gauge cabling with high-current DC connectors for simple installation
- Included mounting brackets support rack-mount installation in 4-post racks using only 2 rack spaces (2U)
- UPDHDEARKIT option supports two-point front-rail rack-mount installation without rear supports
- 2POSTRMKITWM option supports balanced two-point center-mounting in 2-post equipment racks
- 2POSTRMKITWM option also enables wallmount installation
- NOTE: LIMIT OF 1 BP24V28-2U PER UPS, SEE BP24V70-3U or BP24V36-2US FOR MULTI-PACK COMPATIBILITY

Specifications

OVERVIEW	
UPC Code	037332123329
INPUT	
Input Phase	Single-Phase

BATTERY	
DC System Voltage (VDC)	24
UPS Connection	Attached cable with red/black 75 amp male DC connector
Typical Battery Lifespan	4-6 years typical (North America)
PHYSICAL	
Material of Construction	Steel
Rack Height	2U
External Battery Pack Form Factor	Rack
Installation Form Factor Notes	Upright vertical tower configuration is not recommended for this model
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount (2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM); 2-4 post front rail rackmount (Heavy-Duty-2-post-Front-Mounting-Ear-Kit~UPSHDEARKIT); 4 post rackmount short-depth (4-Post-1U-Universal-Adjustable-Rack-Mount-Shelf-Kit-for-Wall-Mount-Racks~4POSTRAILKITWM); Wallmount (2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM)
Minimum Required Rack Depth (cm)	43.18
Minimum Required Rack Depth (inches)	17
Optional Mounting Accessory Notes	2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM ; enables wall-mount and 2-post rackmount installation (Wallmount installation requires that the plastic front bezel of the battery pack face upward); 4-Post-1U-Universal-Adjustable-Rack-Mount-Shelf-Kit-for-Wall-Mount-Racks~4POSTRAILKITWM ; enables installation in 4-post short-depth racks from 14.5 to 23.5 inches (368 to 597mm); Heavy-Duty-2-post-Front-Mounting-Ear-Kit~UPSHDEARKIT ; enables installation in 2 or 4-post racks using front vertical rails only, without rear support
Shipping Dimensions (hwd / in.)	8.90 x 23.40 x 19.80
Shipping Dimensions (hwd / cm)	22.61 x 59.44 x 50.29
Shipping Weight (lbs.)	63.50
Shipping Weight (kg)	28.80
Unit Dimensions (hwd / in.)	3.500 x 17.500 x 14.000
Unit Dimensions (hwd / cm)	8.9 x 44.5 x 35.6
Unit Weight (lbs.)	53.9
Unit Weight (kg)	24.45
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe)
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	2-year limited warranty



Powering Business Worldwide



Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.