

External 24V 3U Rack/Tower Battery Pack for select Tripp Lite UPS Systems (BP24V42-3U)

MODEL NUMBER: BP24V42-3U



Highlights

- Extends runtime of select compatible Tripp Lite UPS Systems with 24VDC external battery connector
- Simple installation; 3U rackmount, tower and stack adaptable
- Supports multi-battery pack installations via built-in daisychain connector

Package Includes

- BP24V42-3U external battery pack
- Mounting hardware
- Warranty information
- Instruction manual

Description

BP24V42-3U rack/tower external battery pack offers extended battery runtime when used in conjunction with compatible Tripp Lite systems. Multi-use form factor supports configuration in stacking, upright tower and rackmount applications using only 3 rack spaces (3U). Supports the connection of multiple BP24V42-3U battery packs via built-in daisychain connector. Includes heavy gauge cabling with high current DC connector for simple installation.

Compatible UPS Systems - OMNIVSINT1500XL, SUINT1000RTXL2Ua and other Tripp Lite UPS systems that specify the use of this battery pack.

Features

- Offers extended-run UPS operation when used in conjunction with compatible Tripp Lite UPS systems
- Supports stacking or rackmount installation using only 3 rack spaces (3U)
- Supports multi-battery pack installation via built-in daisychain connector
- Includes heavy gauge cabling with high current DC connectors for simple installation

Specifications

| OVERVIEW | |
|-------------------------|--------------|
| UPC Code | 37332167484 |
| INPUT | |
| Input Phase | Single-Phase |
| BATTERY | |
| DC System Voltage (VDC) | 24 |



Powering Business Worldwide



| | |
|---|---|
| UPS Connection | Attached cable with red/black 75 amp male DC connector |
| Typical Battery Lifespan | 4-6 years typical (North America) |
| PHYSICAL | |
| Material of Construction | Steel |
| External Battery Pack Form Factor | Rack/Tower |
| Included Mounting Accessory Description | Included 4POSTRAILKIT mounting bracket enables installation in 4 post racks from 20.5 to 36 inches (521 to 914mm) |
| Installation Form Factors Supported with Included Accessories | 4 post 19 inch rackmount |
| Installation Form Factors Supported with Optional Accessories | 2 post rackmount (2 post rackmount); Tower (2-9U STAND) |
| Minimum Required Rack Depth (cm) | 71.12 |
| Minimum Required Rack Depth (inches) | 28 |
| Unit Dimensions (hwd / in.) | 5.250 x 17.500 x 25.000 |
| Unit Dimensions (hwd / cm) | 13.33 x 44.45 x 63.5 |
| Unit Weight (lbs.) | 48.5 |
| Unit Weight (kg) | 22.00 |
| WARRANTY & SUPPORT | |
| Product Warranty Period (U.S. & Canada) | 2-year limited warranty |
| Product Warranty Period (International) | 1-year limited warranty |
| Product Warranty Period (Mexico) | 1-year limited warranty |
| Product Warranty Period (Puerto Rico) | 1-year limited warranty |
| Optional Coverage | 3 year, 5 year, next day and on-site warranty coverage available |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.