

External 24V 3U Rack/Tower Battery Pack for select Tripp Lite UPS Systems (BP24V42-3U)

MODEL NUMBER: BP24V42-3U



Highlights

- Extends runtime of select compatible Tripp Lite UPS Systems with 24VDC external battery connector
- Simple installation; 3U rackmount, tower and stack adaptable
- Supports multi-battery pack installations via built-in daisychain connector

Package Includes

- BP24V42-3U external battery pack
- Mounting hardware
- Warranty information
- Instruction manual

Description

BP24V42-3U rack/tower external battery pack offers extended battery runtime when used in conjunction with compatible Tripp Lite systems. Multi-use form factor supports configuration in stacking, upright tower and rackmount applications using only 3 rack spaces (3U). Supports the connection of multiple BP24V42-3U battery packs via built-in daisychain connector. Includes heavy gauge cabling with high current DC connector for simple installation.

Compatible UPS Systems - OMNIVSINT1500XL, SUINT1000RTXL2Ua and other Tripp Lite UPS systems that specify the use of this battery pack.

Features

- Offers extended-run UPS operation when used in conjunction with compatible Tripp Lite UPS systems
- Supports stacking or rackmount installation using only 3 rack spaces (3U)
- Supports multi-battery pack installation via built-in daisychain connector
- Includes heavy gauge cabling with high current DC connectors for simple installation

Specifications

OVERVIEW	
UPC Code	37332167484
INPUT	
Input Phase	Single-Phase
BATTERY	
DC System Voltage (VDC)	24



Powering Business Worldwide



UPS Connection	Attached cable with red/black 75 amp male DC connector
Typical Battery Lifespan	4-6 years typical (North America)
PHYSICAL	
Material of Construction	Steel
External Battery Pack Form Factor	Rack/Tower
Included Mounting Accessory Description	Included 4POSTRAILKIT mounting bracket enables installation in 4 post racks from 20.5 to 36 inches (521 to 914mm)
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount (2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM); Tower (2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems~2-9USTAND)
Minimum Required Rack Depth (cm)	71.12
Minimum Required Rack Depth (inches)	28
Unit Dimensions (hwd / in.)	5.250 x 17.500 x 25.000
Unit Dimensions (hwd / cm)	13.33 x 44.45 x 63.5
Unit Weight (lbs.)	48.5
Unit Weight (kg)	22.00
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	2-year limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty
Optional Coverage	3 year, 5 year, next day and on-site warranty coverage available

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
 Eaton is a registered trademark. All other trademarks
 are the property of their respective owners.