

External 24V 3U Rack/Tower Battery Pack for select Tripp Lite UPS Systems (BP24V70-3U)

MODEL NUMBER: **BP24V70-3U**



Highlights

- Extends the runtime of expandable 24V DC Tripp Lite UPS Systems
- Included daisychain connector supports the addition of multiple compatible external battery packs
- Supports 3U rackmount installation; 4 post installation accessories included
- Options for 2 post rackmount and tower installation available

Package Includes

- BP24V70-3U external battery pack with attached DC cabling
- 4 post compatible mounting hardware
- Owner's manual

Description

BP24V70-3U rack/tower external battery pack offers extended battery runtime when used in conjunction with expandable 24V Tripp Lite rackmount and tower UPS systems. Includes heavy gauge cabling with high current DC connector for safe, simple installation. Included daisychain connector enables the connection of additional compatible 24V external battery packs to the host UPS. Included mounting accessories support 3U rackmount installation in 4 post racks. Options for 2 post center-mounting and upright tower installation available.

Compatible with these UPS Systems - OMNIVS1500XL, OMNIVSINT1500XL, SMART750RMXL2U, SMART750XLA, SU750RTL2U, SU750RTL2LCD2U, SU750XL, SU1000RTL2UA, SU1000RTL2LCD2U, SU1000XLA, SU1000XLCD, SUIINT1000RTL2UA and other Tripp Lite UPS systems that specify the use of this battery pack.

Features

- Offers extended-run UPS operation when used in conjunction with compatible 24V DC Tripp Lite UPS systems
- Includes heavy gauge cabling with high current DC connectors for simple installation
- Daisychain connector enables the connection of additional compatible 24V external battery packs to the host UPS
- Included mounting brackets support rackmount installation in 4 post racks using only 3 rack spaces (3U)
- 2POSTRMKITHD option supports balanced 2 point center-mounting in 2 post equipment racks
- 2-9USTAND option enables upright tower placement

Specifications

| OVERVIEW | |
|----------|--------------|
| UPC Code | 037332123305 |
| INPUT | |

| | |
|---|---|
| Input Phase | Single-Phase |
| BATTERY | |
| DC System Voltage (VDC) | 24 |
| UPS Connection | Attached cable with red/black 75 amp male DC connector |
| Typical Battery Lifespan | 4-6 years typical (North America) |
| PHYSICAL | |
| Material of Construction | Steel |
| Rack Height | 3U |
| External Battery Pack Form Factor | Rack/Tower |
| Installation Form Factors Supported with Included Accessories | 4 post 19 inch rackmount |
| Installation Form Factors Supported with Optional Accessories | 2 post rackmount (2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM); Tower (2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems~2-9USTAND) |
| Minimum Required Rack Depth (cm) | 71.12 |
| Minimum Required Rack Depth (inches) | 28 |
| Shipping Dimensions (hwd / in.) | 12.00 x 23.00 x 32.50 |
| Shipping Dimensions (hwd / cm) | 30.48 x 58.42 x 82.55 |
| Shipping Weight (lbs.) | 175.00 |
| Shipping Weight (kg) | 79.38 |
| Unit Dimensions (hwd / in.) | 5.250 x 17.500 x 25.000 |
| Unit Dimensions (hwd / cm) | 13.33 x 44.45 x 63.5 |
| Unit Weight (lbs.) | 138.89 |
| Unit Weight (kg) | 63.00 |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS; CE (Europe) |
| WARRANTY & SUPPORT | |
| Product Warranty Period (U.S. & Canada) | 2-year limited warranty |
| Product Warranty Period (International) | 1-year limited warranty |
| Product Warranty Period (Mexico) | 1-year limited warranty |
| Product Warranty Period (Puerto Rico) | 1-year limited warranty |



1000 Eaton Boulevard
Cleveland, OH 44122
United States



© 2022 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.