

External 24V Tower Battery Pack for Tripp Lite SMART1500PSGLCD Gaming UPS Battery Backup

MODEL NUMBER: **BP24V9T**



Provides extended runtime for your 1500VA Pure Sine Wave Gaming UPS, allowing you more time to save your game and shut down your system during power emergencies.

Features

Backup Battery Pack Gives Your Compatible Tripp Lite UPS System Extended Runtime

The BP24V9T offers extended battery runtime when used in conjunction with Tripp Lite's SMART1500PSGLCD Pure Sine Wave Gaming UPS Battery Backup. This allows you an extra 41 minutes of expanded runtime to play through short power failures and to safely save your game and shut down your system in case of a prolonged blackout.

Easy Upright Installation Complements Your Gaming Setup

Heavy-gauge cabling with high-current 24V DC connectors is included for simple installation with the SMART1500PSGLCD on a flat, solid surface where it cannot be tipped over. Required ground wiring is also included. The sleek black housing matches the connected UPS system and looks great with your gaming rig.

Specifications

OVERVIEW	
UPC Code	037332255433
INPUT	
Input Cord Gauge (AWG)	2x10AWG
Input Phase	Single-Phase
Input Cord Details	6 in/15cm length
OUTPUT	

Highlights

- Compatible only with Tripp Lite's SMART1500PSGLCD Gaming UPS Battery Backup
- Includes heavy-gauge cabling with high-current 24V DC ends for easy connection
- Designed for secure upright tower installation on a flat, solid surface
- Sleek black case looks great with the rest of your gaming rig

Applications

Extend the runtime of your compatible Pure Sine Wave Gaming UPS Battery Backup

System Requirements

Compatible only with Tripp Lite's SMART1500PSGLCD Pure Sine Wave Gaming UPS Battery Backup

Package Includes

- BP24V9T External 24V Battery Pack
- External battery cable
- Grounding wire
- Owner's manual

Overload Protection	Set of 2 40A DC fuses
BATTERY	
DC System Voltage (VDC)	0
PHYSICAL	
Material of Construction	ABS
Rack Height	0U
External Battery Pack Form Factor	Tower
Installation Form Factors Supported with Included Accessories	Tower
Shipping Dimensions (hwd / in.)	14.80 x 7.28 x 19.68
Shipping Weight (kg)	11.52
Unit Dimensions (hwd / in.)	11.020 x 4.130 x 16.930
Unit Dimensions (hwd / cm)	27.99 x 10.49 x 43.00
Unit Weight (lbs.)	24.3
Unit Weight (kg)	11.02
ENVIRONMENTAL	
Operating Temperature Range	0°C to 40°C
Storage Temperature Range	-15°C to 40°C
Operating Humidity Range	0%~95% non-condensing
STANDARDS & COMPLIANCE	
Product Certifications	UL 1778
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	2-year limited warranty