

UPS Battery Backup Replacement for Tripp Lite 208V SUT-Series UPS - Batteries Not Included, +/-144VDC

MODEL NUMBER: BP288VEBPNB



UPS battery backup replacement includes internal battery wiring and accessories for 96 user-provided 12V 9Ah batteries.

Features

+/-144VDC UPS Battery Backup Replacement —You Provide the Batteries This special configuration includes the steel enclosure and all required internal wiring and installation accessories for a user-provided quantity of 96 12V 9Ah internal batteries (batteries not included). For the same battery pack with internal batteries included, see Tripp Lite's BP288VEBP.

Gives Your Compatible UPS System Extended Runtime This best UPS battery replacement is compatible only with Tripp Lite's 3-phase 208V SUT20K, SUT30K, SUT40K, SUT60K and other UPS systems that specify the use of this battery pack. After you buy and install your own batteries, the BP288VEBPNB not only provides extended runtime, but it can also be daisy-chained to additional external battery packs for even longer extended-run operation. The three-pole input/output terminal blocks allow safe, simple hardwire installation, as well as internal disconnect for battery isolation.

Rugged Steel Construction Designed to Last in Busy IT Applications The steel cabinet features front and rear doors that provide easy access to the user-supplied internal batteries and the input/output terminal blocks. A 250A circuit breaker protects your equipment from dangerous overcurrent or overloads, while 63A fuses guard each battery string. Pre-installed rolling casters allow you to move the cabinet smoothly to its intended destination. Use the adjustable levelers for secure deployment on a stable surface.

One-Year Warranty The BP288VEBPNB is backed by a one-year warranty, ensuring reliability and performance.

Specifications

Highlights

- Connects to expandable 208V Tripp Lite SUT-Series UPS systems for extended runtime
- Supports daisy-chaining to additional battery packs for even longer runtime
- Front/rear doors provide easy access to 96 user-provided 12V 9Ah internal batteries
- 250A DC breaker protects equipment from potentially hazardous overcurrent
- Pre-installed metal casters allow you to smoothly roll the cabinet to its destination

Applications

- Extend the runtime of your compatible Tripp Lite UPS system to maintain operation during all power conditions
- Daisy-chain to additional battery packs to provide even longer extended-run operation for backing up essential equipment

System Requirements

- Tripp Lite SUT20K, SUT30K, SUT40K, SUT60K or other UPS system specifying compatibility with this external battery pack
- 12V 9Ah sealed valve-regulated lead-acid batteries (VRLA) with F1-type terminals

Package Includes

- BP288VEBPNB UPS Battery Backup Replacement for Tripp Lite 208V SUT-Series UPS
- (24) Battery cartridge kits
- Owner's manual

OVERVIEW

UPC Code	037332213280
----------	--------------



Powering Business Worldwide



INPUT	
Input Phase	3-Phase
BATTERY	
Expandable Runtime	Yes
DC System Voltage (VDC)	+/- 144VDC
UPS Connection	Hardwire (contractor supplies external battery pack wiring - see Owner's Manual for gauge recommendations and complete installation instructions)
Internal Battery Details	Requires a quantity of 96 user-supplied internal batteries (CSB model UPS12580 or equal); All internal battery wiring and mounting hardware included
PHYSICAL	
Material of Construction	Steel
External Battery Pack Form Factor	Tower
Shipping Dimensions (hwd / in.)	30.12 x 26.77 x 37.40
Shipping Dimensions (hwd / cm)	76.50 x 68.00 x 95.00
Shipping Weight (lbs.)	202.83
Shipping Weight (kg)	92.00
Unit Dimensions (hwd / in.)	23.500 x 30.080 x 33.580
Unit Dimensions (hwd / cm)	199.9 x 101.6 x 74.9
Unit Weight (lbs.)	178.57
Unit Weight (kg)	81.00
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.