

External 36V 2U Rack/Tower Battery Pack for select Tripp Lite UPS Systems (BP36V15-2U)

MODEL NUMBER: **BP36V15-2U**



Highlights

- Extends the runtime of compatible 36V Tripp Lite UPS Systems
- Supports 2U rackmount installation; 4 post installation accessories included
- Options for 2 post rackmount, tower and wallmount installation available

Package Includes

- BP36V15-2U external battery pack with attached DC cabling
- 4 post compatible mounting hardware
- Owner's manual

Description

BP36V15-2U rack/tower external battery pack offers extended battery runtime when used in conjunction with expandable 36V Tripp Lite rackmount and tower UPS systems. Includes heavy gauge cabling with high current DC connector for safe, simple installation. Included mounting accessories support 2U rackmount installation in 4 post racks. Options for 2-point front-rail mounting, 2 post center-mounting, wallmount and upright tower installation available.

Compatible with these UPS systems - SMART1000RML2U, SMART1200XLHG, SMART1500RML2Ua, SMART1500XL, SMX1200XLHG, SMX1500XLRT2U and other Tripp Lite UPS systems that specify the use of this battery pack.

Features

- Offers extended-run UPS operation when used in conjunction with compatible 36V DC Tripp Lite UPS systems
- Includes heavy gauge cabling with high current DC connectors for simple installation
- Included mounting brackets support rackmount installation in 4 post racks using only 2 rack spaces (2U)
- UPDHDEARKIT option supports 2 point front-rail rackmount installation without rear supports
- 2POSTRMKITWM option supports balanced 2 point center-mounting in 2 post equipment racks
- 2POSTRMKITWM option also enables wallmount installation
- 2-9USTAND option enables upright tower placement
- NOTE: LIMIT OF 1 BP36V15-2U PER UPS, SEE BP36V42-3U or BP36V27-2US FOR MULTI-PACK COMPATIBILITY

Specifications

OVERVIEW	
UPC Code	037332119919
INPUT	

Input Phase	Single-Phase
BATTERY	
DC System Voltage (VDC)	36
UPS Connection	Grey 2-point connector
Typical Battery Lifespan	4-6 years typical
PHYSICAL	
Material of Construction	Steel
Rack Height	2U
External Battery Pack Form Factor	Rack/Tower
Included Mounting Accessory Description	Included 4POSTRAILKIT mounting bracket enables installation in 4 post racks from 20.5 to 36 inches (521 to 914mm)
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount (2POSTRMKITWM); 4 post rackmount short-depth (4POSTRAILKITWM); Tower (2-9USTAND); Wallmount (2POSTRMKITWM);
Minimum Required Rack Depth (cm)	50.16
Minimum Required Rack Depth (inches)	19.75
Optional Mounting Accessory Notes	Optional 2-9USTAND ; enables upright tower UPS placement; 2POSTRMKITWM ; enables wall-mount and 2-post rackmount installation; 4POSTRAILKITWM ; enables installation in 4-post short-depth racks from 14.5 to 23.5 inches (368 to 597mm)
Shipping Dimensions (hwd / in.)	8.90 x 20.20 x 23.40
Shipping Dimensions (hwd / cm)	22.61 x 51.31 x 59.44
Shipping Weight (lbs.)	57.81
Shipping Weight (kg)	26.22
Unit Dimensions (hwd / in.)	3.500 x 17.500 x 13.250
Unit Dimensions (hwd / cm)	8,89 x 44,45 x 33,66
Unit Weight (lbs.)	45
Unit Weight (kg)	20.41
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe)

TRIPP-LITE

by **EAT•N**

1000 Eaton Boulevard
Cleveland, OH 44122
United States

WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	2-year limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

TRIPP-LITE

by **EAT•N**

© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.