

## TAA-Compliant External 48V 2U Rack/Tower Battery Pack Enclosure for select UPS Systems (BP48V242UTAA-Compliant)

MODEL NUMBER: BP48V242UTAA



### Highlights

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases
- Extends the runtime of compatible 48V Tripp Lite UPS Systems
- Supports 2U rackmount installation; 4 post installation accessories included
- Options for 2 post rackmount, tower and wallmount installation available

### Package Includes

- BP48V242UTAA TAA Compliant external battery pack with attached DC cabling
- 4 post compatible mounting hardware
- Owner's manual

### Description

BP48V242UTAA is compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases. Rack/tower external battery pack offers extended battery runtime when used in conjunction with expandable 48V Tripp Lite rackmount and tower UPS systems. Includes heavy gauge cabling with high current DC connector for safe, simple installation. Included mounting accessories support 2U rackmount installation in 4 post racks. Options for 2-point front-rail mounting, 2 post center-mounting, wallmount and upright tower installation available.

Compatible with these UPS Systems - SM2200RMDVTAA, SMART1500CRMXL, SMART2200CRMXL, SMART2200RMXL2U, SMART2200RMXL2UP, SMART2200RMXLN, SMART2200VSXL, SMART2600RM2U, SMART3000CRMXL, SMART3000RM2U, SMART3000RM2UN, SMART3000RMXL2U, SMART3000RMXLN, SMART3000VS, SMART5000RT3U, SMART5000XFMRXL, SMARTINT3000VS, SMX2200XLRT2U, SMX3000XLRT2UA, SMX5000XLRT3U, SU1500RTLX2UA, SU1500RTLXCD2U, SU1500XL, SU1500XLCD, SU2200RTLX2UA, SU2200RTLXCD2U, SU2200XLA, SU2200XLCD and other Tripp Lite UPS systems that specify the use of this battery pack.

### Features

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.
- Offers extended-run UPS operation when used in conjunction with compatible 48V DC Tripp Lite UPS systems
- Includes heavy gauge cabling with high current DC connectors for simple installation
- Included mounting brackets support rackmount installation in 4 post racks using only 2 rack spaces (2U)
- UPDHDEARKIT option supports 2 point front-rail rackmount installation without rear supports
- 2POSTRMKITWM option supports balanced 2 point center-mounting in 2 post equipment racks
- 2POSTRMKITWM option also enables wallmount installation
- 2-9USTAND option enables upright tower placement
- 48VDCSPLITTER option enables the connection of two BP48V242UTAA external battery packs
- NOTE: LIMIT OF 2 BP48V242UTAA PER UPS (Adding one requires no accessories. Use 48VDCSPLITTER to connect two to the host UPS), SEE BP48V60RT3UTAA, BP48V60RT-3U or BP48V27-2US FOR MULTI-PACK COMPATIBILITY

## Specifications

OVERVIEW	
UPC Code	037332152848
INPUT	
Input Phase	Single-Phase
BATTERY	
DC System Voltage (VDC)	48
Battery Pack Accessory (Optional)	&nbsp;<a class="productLink" href="//www.tripplite.com/Y-Splitter-Cable-for-Tripp-Lite-Battery-Packs-Blue-175A-DC-Connectors-1-ft-0.3-m-48VDCSPLITTER">48VDCSPLITTER</a>&nbsp; (*Limit 2 BP48V242UTAA with &nbsp;<a class="productLink" href="//www.tripplite.com/Y-Splitter-Cable-for-Tripp-Lite-Battery-Packs-Blue-175A-DC-Connectors-1-ft-0.3-m-48VDCSPLITTER">48VDCSPLITTER</a>&nbsp; )
UPS Connection	Attached cable with blue 175 amp DC connector
Typical Battery Lifespan	4-6 years typical (North America)
PHYSICAL	
Rack Height	2U
External Battery Pack Form Factor	Rack/Tower
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount (&nbsp;<a class="productLink" href="//www.tripplite.com/2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM">2POSTRMKITWM</a>&nbsp; ); Wallmount (&nbsp;<a class="productLink" href="//www.tripplite.com/2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM">2POSTRMKITWM</a>&nbsp; ); Tower (&nbsp;<a class="productLink" href="//www.tripplite.com/2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems~2-9USTAND">2-9USTAND</a>&nbsp; ); 2-4 post front rail rackmount (&nbsp;<a class="productLink" href="//www.tripplite.com/Heavy-Duty-2-post-Front-Mounting-Ear-Kit-UPSHDEARKIT">UPSHDEARKIT</a>&nbsp; )
Minimum Required Rack Depth (cm)	52.07
Minimum Required Rack Depth (inches)	20.5
Shipping Dimensions (hwd / in.)	8.70 x 23.50 x 20.00
Shipping Dimensions (hwd / cm)	22.10 x 59.69 x 50.80
Shipping Weight (lbs.)	70.00
Shipping Weight (kg)	31.75
Unit Dimensions (hwd / in.)	3.500 x 17.500 x 13.500
Unit Dimensions (hwd / cm)	8.9 x 44.5 x 34.3
Unit Weight (lbs.)	63
Unit Weight (kg)	28.58
STANDARDS & COMPLIANCE	
Product Certifications	NOM (Mexico)

Product Compliance	RoHS; CE (Europe); Trade Agreements Act (TAA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (U.S. & Canada)	2-year limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty