

## 72V Extended Battery Module (EBM) for SmartOnline UPS Systems, 2U Rack/Tower

MODEL NUMBER: BP72RT



Provides extended runtime for compatible UPS systems in education, healthcare, military, government and other IT applications in small or mid-size networks.

### Features

#### Backup Battery Module Gives Your Compatible UPS System Extended Runtime

The valve-regulated lead-acid (VRLA) BP72RT offers extended battery runtime when used in conjunction with SU2200RTLCD2U, SU2200RTLCDN, SU3000RTLCD2U, SU3000RTLCD2UN, SUINT2200LCD2U and SUINT3000LCD2U SmartOnline® UPS systems. It can also be daisy-chained for a maximum of four matching battery packs to deliver even longer extended-run operation. Heavy-gauge cabling with high-current DC connectors is included for safe, simple installation.

#### Versatile Installation Options

You can mount the BP72RT in 2U of space in an EIA-standard 19-inch rack using the included 4-post rail kit or an optional 2-post rail kit (RK2PC, sold separately). You can also adapt it for tower installation using the UPS system's support stands.

## Specifications

OVERVIEW	
UPC Code	037332279729
INPUT	
Input Phase	Single-Phase
Input Cord Details	15.7 in. connector cord
BATTERY	
Battery Type	Valve Regulated Lead Acid (VRLA)
DC System Voltage (VDC)	72

### Highlights

- Connects to select expandable Tripp Lite series SmartOnline UPS systems to add critical runtime
- Includes heavy-gauge battery cabling with high-current 72V DC connectors
- Daisy-chain connector supports additional battery packs for even longer runtime

### System Requirements

Compatible only with 2023 redesign SU2200RTLCD2U, SU2200RTLCDN, SU3000RTLCD2U, SU3000RTLCD2UN, SUINT2200LCD2U and SUINT3000LCD2U UPS systems

### Package Includes

- 72V Extended Battery Module
- External battery cable
- Rack-mounting hardware
- Quick start guide

Replacement Battery Cartridge	&nbsp;<a class="productLink" href="//tripplite.eaton.com/replacement-battery-for-eaton-9px-ups-and-ebm~744-A3121">744-A3121</a>&nbsp;</td>
Battery Replacement Description	Hot-swappable, user replaceable batteries. EBM requires 2 Replacement Battery Cartridges.
UPS Connection	UPS specific DC connector
<b>PHYSICAL</b>	
Primary Form Factor	Rackmount; Tower
Rack Height	2U
External Battery Pack Form Factor	Rack/Tower
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount (&nbsp;<a class="productLink" href="//tripplite.eaton.com/eaton-2-post-rack-mount-rail-kit-for-9px-ups~RK2PC">RK2PC</a>&nbsp;</td>
Minimum Required Rack Depth (cm)	68.58
Minimum Required Rack Depth (inches)	27
Shipping Dimensions (hwd / in.)	9.40 x 22.80 x 30.30
Shipping Weight (kg)	45.50
Unit Dimensions (hwd / in.)	3.410 x 17.330 x 23.820
Unit Weight (lbs.)	86.4
Unit Weight (kg)	39.19
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Relative Humidity	0-96% non-condensing
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	UL Listed
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (U.S. & Canada)	2-year limited warranty
Extended Service Plans	<b>ADVANCED DEPOT EXCHANGE</b> Service Part Number: 9SW5Y-3000BCParts, electronics and batteries coverageNext business day shippingTechnical support <b>5-YEAR ON-SITE PLAN (US ONLY)</b> Service Part Number: WEBN75XX-7000BCOnsite parts and labor coverage for 5 yearsParts, electronics and batteries coverage24x7 onsite labor coverage, next-day responseNext-day shippingTechnical support



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States



© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.