

Power Cord for Select Eaton Universal PDUs - 17300VA 208V Delta 3-Phase, 460P9W Input, 60A, 10 ft. (3.05 m)

MODEL NUMBER: CBL356-10



PDU power cord with 8-pin universal plug connects your Eaton universal input PDU (UPDU) to a compatible AC outlet.

Features

Detachable Power Cord Supports Universal Input PDU

This detachable power cord is designed for North American 208V Delta 3-phase use. Its 8-pin universal connector mates with an Eaton universal input PDU (UPDU) to meet your diverse rack-power needs. The 10-foot (3.1-meter) length with 460P9W input plug allows you convenient flexibility in placing the UPDU with respect to the AC outlet.

Specifications

OVERVIEW	
UPC Code	786689783860
Device Compatibility	PDU
Country/Region	North America
INPUT	
Input Phase	3-Phase
Maximum Input Amps	60.0
Voltage Compatibility (VAC)	208V 3-Phase Delta
PHYSICAL	
Plug Color	Blue

Highlights

- Delivers 17.3kVA 3-phase power to Eaton's universal input PDU (UPDU)
- 10 ft. length allows flexibility in placing PDU in relationship to AC outlet

System Requirements

Pairs with Eaton's universal input PDU (UPDU)

Package Includes

CBL356-10 Power Cord, 17300VA 3-Phase, 10 ft. (3.05 m)



Powering Business Worldwide

1000 Eaton Boulevard
Cleveland, OH 44122
United States

Cable Jacket Color	Black
Connector Color	Black
Power Cord Jacket Type	W
Cable Outer Diameter (OD)	28mm
Number of Conductors	4
Wire Gauge (AWG)	6
Wire Gauge (OD - mm ²)	6
Cable Length (ft.)	10
Cable Length (m)	3.05
Cable Length (in.)	120
Shipping Dimensions (hwd / in.)	5.00 x 17.00 x 17.00
Shipping Dimensions (hwd / cm)	12.70 x 43.18 x 43.18
Shipping Weight (lbs.)	24.00
Shipping Weight (kg)	10.89
Unit Dimensions (hwd / in.)	4.000 x 11.250 x 10.750
ENVIRONMENTAL	
Operating Temperature Range	32° to 140°F (0° to 60°C)
Storage Temperature Range	32° to 194°F (0° to 90°C)
Operating Temperature	32° to 140°F (0° to 60°C)
Operating Humidity Range	10% TO 90% RH, NON-CONDENSING
Storage Humidity Range	10% TO 90% RH, NON-CONDENSING
CONNECTIONS	
Side A - Connector 1	8-Pin Souriau UTG
Side B - Connector 1	460P9W
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	UL Listed; cTUVus; cUL Listed
Product Compliance	CE (Europe); FCC (USA); RoHS; UKCA; REACH



Powering Business Worldwide

1000 Eaton Boulevard
Cleveland, OH 44122
United States

WARRANTY & SUPPORT

Product Warranty Period
(Worldwide)

3-year limited warranty



Powering Business Worldwide

© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.