



Powering Business Worldwide

Power Cord for Select Eaton Universal PDUs - 11500VA 240V Single-Phase, 360P6W Input, 60A, 10 ft. (3.05 m)

MODEL NUMBER: CBL362-10



Highlights

- Delivers 11.5kVA single-phase power to Eaton's universal input PDU (UPDU)
- 10 ft. length allows flexibility in placing PDU in relationship to AC outlet

System Requirements

Pairs with Eaton's universal input PDU (UPDU)

Package Includes

CBL362-10 Power Cord, 11500VA 240V Single-Phase, 10 ft. (3.05 m)

PDU power cord with 8-pin universal plug connects your Eaton universal input PDU (UPDU) to a compatible AC outlet.

Features

Detachable Power Cord Supports Universal Input PDU

This detachable 11.5kVA power cord is designed for North American 240V single-phase use. Its 8-pin universal connector mates with an Eaton universal input PDU (UPDU) to meet your diverse rack-power needs. The 10-foot (3.1-meter) length with 360P6W input plug allows you convenient flexibility in placing the UPDU with respect to the AC outlet.

Specifications

OVERVIEW	
UPC Code	786689783907
Device Compatibility	PDU
Country/Region	Global
INPUT	
Input Phase	Single-Phase
Maximum Input Amps	60.0
Voltage Compatibility (VAC)	200-240
CONNECTIONS	
Side A - Connector 1	8-Pin Souriau UTG
Side B - Connector 1	360P6W



Powering Business Worldwide

PHYSICAL	
Color	Black
Plug Color	Blue
Cable Jacket Color	Black
Connector Color	Black
Power Cord Jacket Type	SOOW
Cable Outer Diameter (OD)	25mm
Number of Conductors	3
Wire Gauge (AWG)	6
Wire Gauge (OD - mm ²)	6
Cable Length (ft.)	10
Cable Length (m)	3.05
Cable Length (in.)	120
Shipping Dimensions (hwd / in.)	5.00 x 17.00 x 17.00
Shipping Dimensions (hwd / cm)	12.70 x 43.18 x 43.18
Shipping Weight (lbs.)	11.00
Shipping Weight (kg)	4.99
Unit Dimensions (hwd / in.)	4.000 x 11.250 x 10.750
ENVIRONMENTAL	
Operating Temperature Range	32° to 140°F (0° to 60°C)
Storage Temperature Range	32° to 194°F (0° to 90°C)
Operating Temperature	32° to 140°F (0° to 60°C)
Operating Humidity Range	10% TO 90% RH, NON-CONDENSING
Storage Humidity Range	10% TO 90% RH, NON-CONDENSING
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	UL Listed; cTUVus; cUL Listed
Product Compliance	CE (Europe); FCC (USA); RoHS; UKCA; REACH



Powering Business Worldwide

WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.