



Powering Business Worldwide

Power Cord for Select Eaton Universal PDUs - 17300VA 208/120V WYE 3-Phase, 560P9W Input, 60A, 10 ft. (3.05 m)

MODEL NUMBER: CBL366-10



PDU power cord with 8-pin universal plug connects your Eaton universal input PDU (UPDU) to a compatible AC outlet.

Features

Detachable Power Cord Supports Universal Input PDU

This detachable power cord is designed for North American 208/120V WYE 3-phase use. Its 8-pin universal connector mates with an Eaton universal input PDU (UPDU) to meet your diverse rack-power needs. The 10-foot (3.1-meter) length with 560P9W input plug allows you convenient flexibility in placing the UPDU with respect to the AC outlet.

Specifications

OVERVIEW	
UPC Code	786689802073
Device Compatibility	PDU
Country/Region	North America
INPUT	
Input Phase	3-Phase
Maximum Input Amps	60.0
Voltage Compatibility (VAC)	208/120V WYE
CONNECTIONS	
Side A - Connector 1	8-Pin Souriau UTG
Side B - Connector 1	560P9W

Highlights

- Delivers 17.3kVA 3-phase power to Eaton's universal input PDU (UPDU)
- 10 ft. length allows flexibility in placing PDU in relationship to AC outlet

System Requirements

Pairs with Eaton's universal input PDU (UPDU)

Package Includes

CBL366-10 Power Cord, 17300VA 3-Phase, 10 ft. (3.05 m)



Powering Business Worldwide

PHYSICAL	
Plug Color	Blue
Cable Jacket Color	Black
Connector Color	Black
Power Cord Jacket Type	W
Cable Outer Diameter (OD)	28mm
Number of Conductors	4
Wire Gauge (AWG)	6
Wire Gauge (OD - mm ²)	13.3
Cable Length (ft.)	10
Cable Length (m)	3.05
Cable Length (in.)	120
Shipping Dimensions (hwd / in.)	9.00 x 17.00 x 17.00
Shipping Dimensions (hwd / cm)	22.86 x 43.18 x 43.18
Shipping Weight (lbs.)	12.00
Shipping Weight (kg)	5.44
Unit Dimensions (hwd / in.)	4.000 x 11.250 x 10.750
ENVIRONMENTAL	
Operating Temperature Range	32° to 140°F (0° to 60°C)
Storage Temperature Range	32° to 194°F (0° to 90°C)
Operating Temperature	32° to 140°F (0° to 60°C)
Operating Humidity Range	10% TO 90% RH, NON-CONDENSING
Storage Humidity Range	10% TO 90% RH, NON-CONDENSING
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	UL Listed; cTUVus; cUL Listed
Product Compliance	CE (Europe); FCC (USA); RoHS; UKCA; REACH
WARRANTY & SUPPORT	



Powering Business Worldwide

Product Warranty Period (Worldwide)	3-year limited warranty
--	-------------------------

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.