

Multi-Device Charging Station, 16 AC Outlets, iPad and Android Tablets, Wall-Mount and Cart Options, Black

MODEL NUMBER: CS16AC



Locking steel cabinet provides AC charging, secure storage and cord management for up to 16 iPad, Android, Kindle and Surface tablets. For education, office, commercial, retail, industrial and healthcare environments.

Description

The CS16AC 16-Device AC Charging Station Cabinet provides AC charging, secure storage and cord management for up to 16 tablets. It's ideal for education, office, commercial, retail, industrial and healthcare environments.

16 AC outlets provide convenient charging. The charging station is compatible with all devices that charge via user-supplied USB power adapters, including iPad, Android, Kindle, Kindle Fire and Surface tablets and iPhone, Android and Windows smartphones.

The charging station provides comprehensive device protection, with steel construction and a powder-coated finish for long-term durability. It locks with the included keys to prevent device theft, damage or tampering, and flow-through ventilation prevents overheating.

The charging station also provides clutter-free organization of devices and cabling. AC outlets, power adapters and cords store out of sight. Toolless trim panels permit quick service access.

The charging station is easy to configure. It ships fully assembled and supports mounting to a wall, desk, table, counter or floor. The front door opens 180 degrees and side panels are removable for unrestricted device and service access. Removable dividers accommodate thicker devices. You can also convert the charging station to a mobile cart with Tripp Lite's CSHANDLEKIT accessory and roll it where needed.

Features

Highlights

- AC charging and storage for 16 iPad and Android tablets
- Locking steel cabinet with flow-through ventilation
- Adjustable device dividers and integrated cord management
- Ships fully assembled and mounts to wall, desk, table or floor
- 10 ft. power cord and built-in AC outlets for each device

Package Includes

- CS16AC 16-Device AC Charging Station Cabinet
- (2) Keys for door lock
- Owner's manual



Convenient Charging

- 16 AC outlets charge up to 16 iPad, Android, Kindle or Surface tablets
- Compatible with all devices that charge via user-supplied USB power adapters, including iPad, Android, Kindle, Kindle Fire and Surface tablets and iPhone, Android and Windows smartphones
- 10 ft. AC input cord reaches distant outlets

Comprehensive Protection

- Sturdy steel construction and powder-coated finish provide long-term durability
- Door locks with included keys to prevent device theft, damage or tampering
- Flow-through ventilation prevents devices from overheating
- Coated shelf shields devices from scratches and scuffs
- Built-in circuit breaker protects against overloads

Clutter-Free Organization

- AC outlets, device AC adapters and cords store out of sight
- Shelf includes charging cord access ports for each device
- Toolless trim panels permit quick access to AC adapters and cords
- Outlets spaced to fit bulky power adapters without blocking adjacent outlets

Flexible Configuration

- Ships fully assembled
- Supports mounting to wall, desk, table, counter or floor
- Converts to mobile cart with optional CSHANDLEKIT accessory
- Door opens 180 degrees and side panels are removable for clear access
- Removable dividers accommodate thicker devices like battery chargers

Specifications

OVERVIEW	
UPC Code	037332185235
Product Type	Multi-Device Charger
Charging Form Factor	Stationary Cabinet
Functions	Charge; Secure
Device Compatibility	Tablet; Phone
Device Slots	16
INPUT	
Nominal Input Voltage(s) Supported	120V AC



Input Frequency	50 / 60 Hz
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
CHARGING	
Charging Ports / Amps	(16) 12A
Number of Charging Ports	16
Overcharge Protection	No
Charging Method	AC
Charging Ports Detail	Pass through
Charging Port Type	NEMA 5-15R
Charging Amps per Port	12A
PHYSICAL	
Antimicrobial Coating	No
Charging Station Form Factor	Stationary Cabinet
Color	Black
Material of Construction	Steel
Shipping Dimensions (hwd / cm)	61.60 x 67.01 x 61.29
Shipping Dimensions (hwd / in.)	24.25 x 26.38 x 24.13
Shipping Weight (kg)	44.00
Shipping Weight (lbs.)	97.00
Slot Dimensions (hwd / in.)	11.6 x 0.8 x 13.9
Slot Dimensions (hwd / mm)	295 x 20.1 x 353.8
Unit Dimensions (hwd / cm)	54.86 x 59.94 x 54.86
Unit Dimensions (hwd / in.)	21.6 x 23.6 x 21.6
Unit Weight (kg)	32.66
Unit Weight (lbs.)	72
Number of Shelves	1
SPECIAL FEATURES	
Cord Management	Yes
EMI/RFI Line Noise Protection	No
Locking	Yes
Lock Type	Key



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Built-In Circuit Breaker	Yes
Overcurrent Protection	Yes
Flow-Through Ventilation	Yes
UV Sterilization	No
STANDARDS & COMPLIANCE	
Certifications	Tested to EIA-310-E, UL60950, FCC & IEC Class B
Approvals	RoHS
NOM (Mexico)	Tested to NOM (Mexico)
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty
CATEGORY PAGE FILTERS (Y/N ONLY)	
External Receptacle	No

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>