

## Multi-Device Charging Station, 16 USB Ports, iPad and Android Tablets, Wall-Mount Option, White

MODEL NUMBER: **CS16USBW**



Locking steel cabinet provides 2.4A USB charging, syncing, secure storage and cord management for up to 16 tablets and other USB devices. Recommended for education, office, commercial, retail, industrial and healthcare environments.

### Description

The CS16USBW 16-Device USB Charging Station Cabinet provides fast charging, convenient syncing, secure storage and cord management for up to 16 iPad, Android, Surface and Kindle tablets, as well as mobile phones and other USB devices. It's recommended for education, office, commercial, retail, industrial and healthcare environments.

16 USB ports deliver the fastest charging supported by each device, up to 2.4A per port. The charging station also supports wired and wireless syncing, including syncing while charging.

The steel cabinet promotes comprehensive device protection with steel construction and a white powder-coated finish for long-term durability. It locks with the included keys to help prevent device theft, damage or tampering. Flow-through ventilation protects against overheating, and the coated shelf helps prevent scratches and scuffs. The charging station also provides clutter-free organization of devices and cabling.

The CS16USBW is easy to configure. It ships fully assembled and supports mounting to a wall, desk, table, counter or floor. The front door opens 180 degrees for improved device and service access, and removable dividers accommodate thicker devices.

### Features

#### Fast Charging

- 16 USB ports provide fastest charging supported by each device, up to 2.4A per port

### Highlights

- Fast 2.4A USB charging, syncing and storage for 16 tablets
- Locking steel cabinet with flow-through ventilation
- Adjustable device dividers and integrated cord management
- Ships fully assembled and mounts to wall, desk, table or floor
- Detachable 10 ft. power cord

### Package Includes

- CS16USBW 16-Device USB Charging Station Cabinet, White
- Detachable 10 ft. AC input cord w/NEMA 5-15P plug
- (2) Keys
- Owner's manual



- Recommended for iPad®, Android™, Surface™ and Kindle™ tablets
- Also charges mobile phones and other USB devices
- Detachable 10 ft. AC input cord with NEMA 5-15P plug

#### Convenient Syncing

- USB sync uplink port connects to host computer for wired syncing
- Compatible with wireless syncing
- Supports simultaneous syncing and charging (up to 1.5A per port during wired syncing)

#### Comprehensive Protection

- Sturdy steel construction and powder-coated finish promote long-term durability
- Door locks with included keys to help prevent device theft, damage or tampering
- Flow-through ventilation helps prevent devices from overheating
- Coated shelf shields devices from scratches and scuffs

#### Flexible Configuration

- Ships fully assembled
- Supports mounting to wall, desk, table, counter or floor
- Door opens 180 degrees for improved device and service access
- Removable dividers accommodate thicker devices
- Firmware upgrade port for future updates

## Specifications

OVERVIEW	
UPC Code	037332188946
Product Type	Multi-Device Charger
Charging Form Factor	Stationary Cabinet
Functions	Charge; Secure; Sync
Device Compatibility	Tablet; Phone
Device Slots	16
INPUT	
Nominal Input Voltage(s) Supported	120V AC; 230V AC
Voltage Compatibility (VAC)	110-240
Input Frequency	50 / 60 Hz (auto-select)
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10



Input Cord Length (m)	3.05
<b>CHARGING</b>	
Charging Ports / Amps	(16) 2.4A
Number of Charging Ports	16
Overcharge Protection	Yes
Total Charging Amps	40A
Charging Method	USB
Charging Ports Detail	Pass through
Charging Port Type	USB A (FEMALE)
Charging Amps per Port	2.4A
<b>PHYSICAL</b>	
Antimicrobial Coating	No
Charging Station Form Factor	Stationary Cabinet
Color	White
Material of Construction	Steel
Shipping Dimensions (hwd / cm)	46.99 x 54.00 x 69.01
Shipping Dimensions (hwd / in.)	18.50 x 21.26 x 27.17
Shipping Weight (kg)	27.67
Shipping Weight (lbs.)	61.00
Slot Dimensions (hwd / in.)	8.1 x 0,8 x 13,9
Slot Dimensions (hwd / mm)	206 x 20,1 x 353.8
Unit Dimensions (hwd / cm)	37.01 x 59.99 x 45.01
Unit Dimensions (hwd / in.)	14.57 x 23.62 x 17.72
Unit Weight (kg)	25.01
Unit Weight (lbs.)	55.14
Number of Shelves	1
<b>ENVIRONMENTAL</b>	
Power Consumption (Watts)	56W
<b>SPECIAL FEATURES</b>	
Cord Management	Yes
EMI/RFI Line Noise Protection	Yes
Locking	Yes
Lock Type	Key



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Built-In Circuit Breaker	Yes
Overcurrent Protection	Yes
Flow-Through Ventilation	Yes
UV Sterilization	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to EIA-310-E, UL60950, FCC & IEC Class B
Approvals	RoHS
NOM (Mexico)	Tested to NOM (Mexico)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	2-year limited warranty
<b>CATEGORY PAGE FILTERS (Y/N ONLY)</b>	
External Receptacle	No

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>