

## Multi-Device Charging Station, 32 USB Ports, iPad and Android Tablets, Wall-Mount and Cart Options, Black

MODEL NUMBER: CS32USB



### Highlights

- Fast 2.4A USB charging, syncing and storage for 32 devices
- Locking steel cabinet with flow-through ventilation
- Adjustable device dividers and integrated cord management
- Ships fully assembled and mounts to wall, desk, table or floor
- Detachable 10 ft. power cord

### Package Includes

- CS32USB 32-Device USB Charging Station Cabinet
- (2) Keys for door lock
- Detachable 10 ft. AC input cord
- Owner's manual

Locking steel cabinet provides 2.4A USB charging, syncing, secure storage and cord management for up to 32 tablets and other USB devices. For education, office, commercial, retail, industrial and healthcare environments.

### Description

The CS32USB 32-Device USB Charging Station Cabinet provides fast charging, convenient syncing, secure storage and cord management for up to 32 iPad, Android, Surface and Kindle tablets. It also charges mobile phones and other USB devices. It's ideal for education, office, commercial, retail, industrial and healthcare environments.

32 USB ports deliver the fastest charging supported by each device, up to 2.4A per port. The charging station also supports wired and wireless syncing, including syncing while charging.

The steel cabinet provides comprehensive device protection. It has a powder-coated finish and locks with the included keys to prevent device theft, damage or tampering. Flow-through ventilation prevents overheating, the coated shelves prevent scratches and scuffs, and the charging station also provides clutter-free organization of devices and cabling.

The charging station is easy to configure. It ships fully assembled and supports mounting to a wall, desk, table, counter or floor. The front door opens 180 degrees for clear access, and removable dividers accommodate thicker devices. You can also convert the charging station to a mobile cart with Tripp Lite's CSHANDLEKIT accessory.

### Features

#### Fast Charging

- 32 USB ports provide fastest charging supported by each device, up to 2.4A per port
- Perfect for iPad, Android, Surface and Kindle tablets

- Also charges mobile phones and other USB devices
- Detachable 10 ft. AC input cord

**Convenient Syncing**

- USB sync uplink port connects to host computer for wired syncing
- Also compatible with wireless syncing
- Supports simultaneous syncing and charging (up to 1.5A per port during wired syncing)

**Comprehensive Protection**

- Sturdy steel construction and powder-coated finish provide long-term durability
- Door locks with included keys to prevent device theft, damage or tampering
- Flow-through ventilation prevents devices from overheating
- Coated shelves shield devices from scratches and scuffs

**Flexible Configuration**

- Ships fully assembled
- Supports mounting to wall, desk, table, counter or floor
- Door opens 180 degrees for unrestricted device and service access
- Removable dividers accommodate thicker devices
- Firmware upgrade port for future updates
- Converts to mobile cart with optional CSHANDLEKIT accessory

## Specifications

OVERVIEW	
UPC Code	037332185426
INPUT	
Input Connection Type	C14 inlet with 100-250V AC compatibility. Also accepts user-supplied country-specific AC cordsets
Voltage Compatibility (VAC)	110-240
Input Frequency	50 / 60 Hz (auto-select)
CHARGING	
Charging Method	USB
Charging Ports / Amps	(32) 2.4A
PHYSICAL	
Color	Black
Charging Station Form Factor	Stationary Cabinet
Shipping Dimensions (hwd / in.)	30.51 x 28.35 x 26.38
Shipping Dimensions (hwd / cm)	77.50 x 72.01 x 67.01



Powering Business Worldwide



Shipping Weight (lbs.)	130.07
Shipping Weight (kg)	59.00
Slot Dimensions - Bottom (hwd / in.)	8.0 x 0.8 x 13.9
Slot Dimensions - Bottom (hwd / mm)	204 x 20.1 x 353.8
Slot Dimensions - Top (hwd / in.)	8.1 x 0.8 x 13.9
Slot Dimensions - Top (hwd / mm)	206 x 20.1 x 353.8
Unit Dimensions (hwd / in.)	25.080 x 23.620 x 21.570
Unit Dimensions (hwd / cm)	63.75 x 59.94 x 54.86
Unit Weight (lbs.)	96
Unit Weight (kg)	43.54
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.