

16-Device AC Charging Station Cabinet for Chromebooks and Laptops, Wall-Mount and Cart Options, White

MODEL NUMBER: CSC16ACW



Locking steel cabinet provides AC charging, secure storage and cord management for up to 16 Chromebooks and laptops. Recommended for education, office, commercial, retail, industrial and healthcare environments.

Description

The CSC16ACW 16-Device AC Charging Station Cabinet provides AC charging, secure storage and cord management for up to 16 Chromebooks and laptops. It's recommended for education, office, commercial, retail, industrial and healthcare environments.

16 AC outlets provide convenient charging for Chromebooks and laptops with a screen size up to 15 inches. Their AC adapters plug into the cabinet's 16 NEMA 5-15R outlets as needed, up to 1,440 total watts. The CSC16ACW also charges tablets and other USB devices through their power adapters. A built-in circuit breaker protects against overloads. The 10-foot AC input cord with NEMA 5-15P plug reaches distant outlets to help you place the cart in a convenient location.

The cabinet promotes comprehensive device protection with steel construction and a white powder-coated finish for long-term durability. It locks with the included keys to help prevent device theft, damage or tampering, and flow-through ventilation helps prevent overheating.

The cabinet also encourages clutter-reducing organization of devices and cabling. AC outlets, power adapters and cords store out of sight. A toolless trim panel permits quick service access.

The cabinet is easy to configure. The cabinet It ships fully assembled. and supports mounting to a wall, desk, table, counter or floor. The front doors open 180 degrees for improved device and service access. Rear-panel slots support optional wall-mount installation, and removable dividers accommodate thicker devices. You can also convert it the cabinet to a mobile cart with Tripp Lite's optional CSHANDLEKIT2 (sold separately), and roll it where needed.

Features

Convenient Charging Charges 16 Chromebooks and laptops up to 15 in. screen size
Device power adapters plug into NEMA 5-15R outlets (up to 1,440 watts total)
Also charges tablets and other USB devices through their power adapters
Built-in circuit breaker protects against overloads
10 ft. AC input cord with NEMA 5-15P plug reaches distant outlets

Highlights

- Charges 16 Chromebooks and laptops up to 15 in. screen size
- Secures devices in locking, vented steel cabinet with cart option
- Protective shelf with removable dividers and cord management
- Supports mounting to wall, desk, table, counter or floor
- Ships fully assembled for quick, easy installation

Package Includes

- CSC16ACW 16-Device AC Charging Station Cabinet, White
- (2) Keys
- Owner's manual



Comprehensive Protection Sturdy steel construction and powder-coated finish promote long-term durability. Doors lock with included keys to help prevent device theft, damage or tampering. 3-point locking mechanism latches doors at top, middle and bottom. Built-in hasp and user-supplied padlock can replace or supplement built-in lock. Rear ports accommodate user-supplied bicycle cable or chain lock. Flow-through ventilation helps prevent devices from overheating. Protective shelf specially coated to avoid device scratches and scuffs. Cord access ports with rubber grommets protect against abrasions. Solid top work surface helps avoid accidental drips and spills that could damage devices.

Clutter-Reducing Organization AC outlets, power adapters and cords store out of sight. Toolless trim panel permits quick access to AC adapters and cords. Shelf includes charging cord access ports for each device. Staggered outlets fit power adapters without blocking adjacent outlets.

Flexible Configuration Ships fully assembled for quick, easy installation. Supports mounting to wall, desk, table, counter or floor. Split front doors open 180 degrees for improved device and service access. Removable dividers accommodate thicker devices like battery chargers. Converts to mobile cart with optional CSHANDLEKIT2 (sold separately).

Specifications

OVERVIEW	
UPC Code	037332194817
OUTPUT	
Charging Ports / Amps	(16) 12A
Charging Method	AC
INPUT	
Voltage Compatibility (VAC)	120
Input Frequency	50 / 60 Hz
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
PHYSICAL	
Charging Station Form Factor	Stationary Cabinet
Color	White
Shipping Dimensions (hwd / cm)	62.31 x 59.99 x 85.50
Shipping Dimensions (hwd / in.)	24.53 x 23.62 x 33.66
Shipping Weight (kg)	47.17
Shipping Weight (lbs.)	104.00
Slot Dimensions (hwd / in.)	10.6 x 1.5 x 15.4
Slot Dimensions (hwd / mm)	268.1 x 38.2 x 390.5
Unit Dimensions (cm)	47.54 x 77.04 x 54.86
Unit Dimensions (hwd / cm)	47.54 x 77.04 x 54.86



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Unit Dimensions (hwd / in.)	18.8 x 30.3 x 21.6
Unit Weight (kg)	34.10
Unit Weight (lbs.)	75.17
CERTIFICATIONS	
Certifications	Tested to EIA-310-E, FCC & IEC Class B, UL 1363 (Power Component)
NOM (Mexico)	Tested to NOM (Mexico)
Approvals	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>