

16-Device USB Charging Station Cabinet with Sync for iPad and Android Tablets, Wall-Mount and Cart Options, Black

MODEL NUMBER: **CSC16USB**



Locking steel cabinet provides 2.4A USB charging, syncing, secure storage and cord management for up to 16 tablets and other devices. Recommended for education, office, commercial, retail, industrial and healthcare environments.

Features

Fast Charging

- 16 USB ports provide fastest charging supported by each device, up to 2.4A per port
- Recommended for iPad, Android, Surface and Kindle tablets
- Also charges mobile phones and other USB devices
- Fits tablets with cases (up to 16.5 x 10.5 x 1.5 in. with cord)
- 10-ft. (3.05 m) AC input cord with NEMA 5-15P plug reaches distant outlets

Convenient Syncing

- USB uplink port connects to host computer for wired syncing
- Supports wireless syncing and simultaneous syncing/charging (up to 1.5A per port during wired syncing)

Comprehensive Protection

- Sturdy steel construction and powder-coated finish promote long-term durability
- Doors lock with included keys to help prevent device theft, damage or tampering
- 3-point locking mechanism latches doors at top, middle and bottom
- Built-in hasp and user-supplied padlock can replace or supplement built-in lock
- Rear ports accommodate user-supplied bicycle cable or chain lock
- Flow-through ventilation helps prevent devices from overheating
- Protective shelf specially coated to avoid device scratches and scuffs
- Cord access ports with rubber grommets protect against abrasions

Highlights

- Fast 2.4A USB charging and syncing for 16 tablets
- Secures devices in locking, vented steel cabinet with cart option
- Protective shelf with removable dividers and cord management
- Supports mounting to wall, desk, table, counter or floor
- Ships fully assembled for quick, easy installation

Package Includes

- CSC16USB 16-Device USB Charging Station Cabinet, Black
- (2) Keys
- Owner's manual



- Solid top work surface helps avoid accidental drips and spills that could damage devices

Clutter-Reducing Organization

- USB ports and charging cords store out of sight
- Shelf includes charging cord access ports for each device
- Toolless trim panel permits quick access to cords

Flexible Configuration

- Ships fully assembled for quick, easy installation
- Supports mounting to wall, desk, table, counter or floor
- Split front doors open 180 degrees for improved device and service access
- Removable dividers accommodate thicker devices like battery chargers
- Firmware upgrade port for future updates
- Converts to mobile cart with optional CSHANDLEKIT2 (sold separately)

Specifications

OVERVIEW	
UPC Code	037332194640
Product Type	Multi-Device Charger
Charging Form Factor	Stationary Cabinet
Functions	Charge; Secure; Sync
Device Compatibility	Tablet
Device Slots	16
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Voltage Compatibility (VAC)	110; 120
Input Frequency	50 / 60 Hz (auto-select)
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
CHARGING	
Number of Charging Ports	16
Total Charging Amps	40A
Total Charging Watts	200
Charging Method	USB



Charging Port Type	USB A (FEMALE)
Charging Ports Details	Pass through
Charging Ports / Amps	(16) 2.4A
Overcharge Protection	Yes
Charging Amps per Port	2.4A
PHYSICAL	
Color	Black
Antimicrobial	No
Charging Station Form Factor	Stationary Cabinet
Material of Construction	Steel
Shipping Dimensions (hwd / cm)	62.31 x 59.99 x 85.50
Shipping Dimensions (hwd / in.)	24.53 x 23.62 x 33.66
Shipping Weight (kg)	50.80
Shipping Weight (lbs.)	112.00
Slot Dimensions (hwd / in.)	10.6 x 1.5 x 15.4
Slot Dimensions (hwd / mm)	268.1 x 38.2 x 390.5
Unit Dimensions (hwd / cm)	47.75 x 77.04 x 54.86
Unit Dimensions (hwd / in.)	18.8 x 30.33 x 21.6
Unit Weight (kg)	38.40
Unit Weight (lbs.)	84.66
Number of Shelves	1
ENVIRONMENTAL	
Power Consumption (Watts)	56
FEATURES & SPECIFICATIONS	
Cord Management	Yes
EMI/RFI Line Noise Protection	Yes
Locking	Yes
Lock Type	Key
Built-In Circuit Breaker	Yes
Overcurrent Protection	Yes
Flow-Through Ventilation	Yes
UV Sterilization	No
STANDARDS & COMPLIANCE	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Certifications	Tested to EIA-310-E, UL60950, FCC & IEC Class B
Approvals	RoHS
NOM (Mexico)	Tested to NOM (Mexico)
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty
CATEGORY PAGE FILTERS (Y/N ONLY)	
External Receptacle	No

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>