

## Multi-Device Charging Cart, 32 AC Outlets, Chromebooks and Laptops, Wall-Mount Option, Black

MODEL NUMBER: **CSC32AC**



Locking steel cart provides AC charging, secure storage and cord management for up to 32 Chromebooks and laptops. Recommended for education, office, commercial, retail, industrial and healthcare environments.

### Description

The CSC32AC 32-Device AC Charging Station Cart provides AC charging, secure storage and cord management for up to 32 Chromebooks and laptops. It's recommended for education, office, commercial, retail, industrial and healthcare environments.

32 AC outlets provide convenient charging for Chromebooks and laptops with a screen size up to 15 inches. Their AC adapters plug into the cart's 32 NEMA 5-15R outlets as needed, up to 1,440 total watts. The CSC32AC also charges tablets and other USB devices through their power adapters. A built-in circuit breaker protects against overloads. The 10-ft. (3.05 m) AC input cord with NEMA 5-15P plug reaches distant outlets to help you place the cart in a convenient location.

The cart promotes comprehensive device protection with steel construction and a black powder-coated finish for long-term durability. It locks with the included keys to help prevent device theft, damage or tampering, and flow-through ventilation helps prevent overheating.

The cart also encourages clutter-reducing organization of devices and cabling. AC outlets, power adapters and cords store out of sight. Toolless trim panels permit quick service access.

When moving devices from room to room, the cart provides convenient mobility. Large swivel casters with non-marking wheels improve the ride over uneven surfaces and lock to help prevent unwanted movement at rest. The reversible wide-grip handle assists cart control.

The cart is easy to configure. It ships ready for quick, easy installation, and the handle and cord wrap attach on either side. The split front doors open 180 degrees for improved device and service access. Rear-panel slots support optional wall-mount installation, and removable shelf dividers accommodate thicker devices.

### Features

**Convenient Charging** Charges 32 Chromebooks and laptops up to 15 in. screen size  
Device power adapters plug into NEMA 5-15R outlets (up to 1,440 watts total)  
Also charges tablets and other USB devices through their power adapters  
Built-in circuit breaker protects against overloads  
10-ft. (3.05 m) AC input cord with NEMA 5-15P plug reaches distant outlets

**Comprehensive Protection** Sturdy steel construction and powder-coated finish promote long-term durability  
Doors lock with included keys to help prevent device theft, damage or tampering  
3-point locking mechanism latches doors at top, middle and bottom  
Built-in hasp and user-supplied padlock can replace or supplement built-in lock  
Rear ports accommodate user-supplied bicycle cable or chain lock  
Flow-through

### Highlights

- Charges 32 Chromebooks and laptops up to 15 in. screen size
- Secures devices in locking, vented, wall-mountable steel cart
- Protective shelves with removable dividers and cord management
- Wide-grip handle and locking casters with non-marking wheels
- Ships ready for quick, easy installation

### Package Includes

- CSC32AC 32-Device AC Charging Station Cart, Black
- Cart handle
- Input cord wrap
- Hex key
- Mounting hardware for handle and cord wrap
- (2) Keys
- Owner's manual

ventilation helps prevent devices from overheating  
Protective shelves specially coated to avoid device scratches and scuffs  
Cord access ports with rubber grommets protect against abrasions  
Solid top work surface helps avoid accidental drips and spills that could damage devices

**Clutter-Reducing Organization** AC outlets, power adapters and cords store out of sight  
Toolless trim panels permit quick access to AC adapters and cords  
Shelves include charging cord access ports for each device  
Staggered outlets fit power adapters without blocking adjacent outlets

**Effortless Mobility** Large swivel casters with non-marking wheels improve ride over uneven surfaces  
Casters lock to help prevent unwanted movement at rest  
Reversible wide-grip handle assists cart control  
Reversible cord wrap keeps input cord out of the way when moving cart  
Compact cart fits in same space as typical utility cart

**Flexible Configuration** Ships ready for quick, easy installation—just attach handle and cord wrap  
Split front doors open 180 degrees for improved device and service access  
Rear-panel mounting slots support optional wall-mount installation  
Removable dividers accommodate thicker devices like battery chargers

## Specifications

OVERVIEW	
UPC Code	037332191809
Product Type	Multi-Device Charger
Charging Form Factor	Mobile Cart
Functions	Charge; Secure
Device Compatibility	Chromebook; Laptop
Device Slots	32
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Voltage Compatibility (VAC)	120
Input Frequency	50 / 60 Hz
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
CHARGING	
Number of Charging Ports	32
Charging Method	AC
Charging Port Type	NEMA 5-15R
Charging Ports Details	Pass through
Charging Ports / Amps	(32) 12A
Overcharge Protection	No

Charging Amps per Port	12A
<b>PHYSICAL</b>	
Color	Black
Material of Construction	Steel
Charging Station Form Factor	Mobile Cart
Shipping Dimensions (hwd / in.)	45.08 x 22.83 x 33.66
Shipping Dimensions (hwd / cm)	114.50 x 57.99 x 85.50
Shipping Weight (lbs.)	166.00
Shipping Weight (kg)	75.30
Slot Dimensions - Bottom (hwd / in.)	10.5 x 1.5 x 15.4
Slot Dimensions - Bottom (hwd / mm)	266.7 x 38.2 x 390.5
Slot Dimensions - Top (hwd / in.)	10.5 x 1.5 x 15.4
Slot Dimensions - Top (hwd / mm)	266.7 x 38.2 x 390.5
Unit Dimensions (hwd / in.)	36.100 x 34.800 x 20.200
Unit Dimensions (hwd / cm)	106.76 x 88.39 x 54.86 (with handle installed)
Unit Weight (lbs.)	130.67
Unit Weight (kg)	59.27
Number of Shelves	2
Assembly Required	Yes
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antimicrobial	No
Built-In Circuit Breaker	Yes
Cord Management	Yes
Overcurrent Protection	Yes
EMI/RFI Line Noise Protection	No
Flow-Through Ventilation	Yes
IP68 Rated	No
IP20 Rated	No
UV Sterilization	No
Locking	Yes
Lock Type	Key
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	NOM (Mexico); UL 1363

# TRIPP-LITE

by **EAT•N**

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States

Product Compliance	RoHS; CE (Europe); EIA/ECA-310-E; REACH; FCC Part 15 Class B (USA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	2-year limited warranty
<b>CATEGORY PAGE FILTERS (Y/N ONLY)</b>	
External Receptacle	No

# TRIPP-LITE

by **EAT•N**

© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.