# Multi-Device Charging Cart, 32 AC Outlets, Chromebooks and Laptops, Wall-Mount Option, Black

MODEL NUMBER: **CSC32AC**

Locking steel cart provides AC charging, secure storage and cord management for up to 32 Chromebooks and laptops. Recommended for education, office, commercial, retail, industrial and healthcare environments.

## Description

The CSC32AC 32-Device AC Charging Station Cart provides AC charging, secure storage and cord management for up to 32 Chromebooks and laptops. It's recommended for education, office, commercial, retail, industrial and healthcare environments.
32 AC outlets provide convenient charging for Chromebooks and laptops with a screen size up to 15 inches. Their AC adapters plug into the cart's 32 NEMA 5-15R outlets as needed, up to 1,440 total watts. The CSC32AC also charges tablets and other USB devices through their power adapters. A built-in circuit breaker protects against overloads. The 10-ft. (3.05 m) AC input cord with NEMA 5-15P plug reaches distant outlets to help you place the cart in a convenient location.
The cart promotes comprehensive device protection with steel construction and a black powder-coated finish for long-term durability. It locks with the included keys to help prevent device theft, damage or tampering, and flow-through ventilation helps prevent overheating.
The cart also encourages clutter-reducing organization of devices and cabling. AC outlets, power adapters and cords store out of sight. Toolless trim panels permit quick service access.
When moving devices from room to room, the cart provides convenient mobility. Large swivel casters with non-marking wheels improve the ride over uneven surfaces and lock to help prevent unwanted movement at rest. The reversible wide-grip handle assists cart control.
The cart is easy to configure. It ships ready for quick, easy installation, and the handle and cord wrap attach on either side. The split front doors open 180 degrees for improved device and service access. Rear-panel slots support optional wall-mount installation, and removable shelf dividers accommodate thicker devices.

## Features

**Convenient Charging**Charges 32 Chromebooks and laptops up to 15 in. screen sizeDevice power adapters plug into NEMA 5-15R outlets (up to 1,440 watts total)Also charges tablets and other USB devices through their power adaptersBuilt-in circuit breaker protects against overloads10-ft. (3.05 m) AC input cord with NEMA 5-15P plug reaches distant outlets

**Comprehensive Protection**Sturdy steel construction and powder-coated finish promote long-term durabilityDoors lock with included keys to helps prevent device theft, damage or tampering3-point locking mechanism latches doors at top, middle and bottomBuilt-in hasp and user-supplied padlock can replace or supplement built-in lockRear ports accommodate user-supplied bicycle cable or chain lockFlow-through ventilation helps prevent devices from overheatingProtective shelves specially coated to avoid device scratches and scuffsCord access ports with rubber grommets protect against abrasionsSolid top work

## Highlights

- Charges 32 Chromebooks and laptops up to 15 in. screen size
- Secures devices in locking, vented, wall-mountable steel cart
- Protective shelves with removable dividers and cord management
- Wide-grip handle and locking casters with non-marking wheels
- Ships ready for quick, easy installation

## Package Includes

- CSC32AC 32-Device AC Charging Station Cart, Black
- Cart handle
- Input cord wrap
- Hex key
- Mounting hardware for handle and cord wrap
- (2) Keys
- Owner’s manual

surface helps avoid accidental drips and spills that could damage devices

**Clutter-Reducing Organization**AC outlets, power adapters and cords store out of sightToolless trim panels permit quick access to AC adapters and cordsShelves include charging cord access ports for each deviceStaggered outlets fit power adapters without blocking adjacent outlets

**Effortless Mobility**Large swivel casters with non-marking wheels improve ride over uneven surfacesCasters lock to help prevent unwanted movement at restReversible wide-grip handle assists cart controlReversible cord wrap keeps input cord out of the way when moving cartCompact cart fits in same space as typical utility cart

**Flexible Configuration**Ships ready for quick, easy installation—just attach handle and cord wrapSplit front doors open 180 degrees for improved device and service accessRear-panel mounting slots support optional wall-mount installationRemovable dividers accommodate thicker devices like battery chargers

# Specifications

| | |
|---|---|
| **OVERVIEW** | |
| UPC Code | 037332191809 |
| Product Type | Multi-Device Charger |
| Charging Form Factor | Mobile Cart |
| Charger Functions | Charge; Secure |
| Device Compatibility | Chromebook; Laptop |
| Device Slots | 32 |
| **INPUT** | |
| Nominal Input Voltage(s) Supported | 120V AC |
| Voltage Compatibility (VAC) | 120 |
| Input Frequency | 50 / 60 Hz |
| Input Plug Type | NEMA 5-15P |
| Input Cord Length (ft.) | 10 |
| Input Cord Length (m) | 3.05 |
| **OUTPUT** | |
| Frequency Compatibility | 50 / 60 Hz |
| **CHARGING** | |
| Number of Charging Ports | 32 |
| Charging Method | AC |
| Charging Port Type | NEMA 5-15R |
| Charging Ports Details | Pass through |
| Charging Ports / Amps | (32) 12A |
| Overcharge Protection | No |

| | |
|---|---|
| Charging Amps per Port | 12A |
| **PHYSICAL** | |
| Color | Black |
| Material of Construction | Steel |
| Charging Station Form Factor | Mobile Cart |
| Shipping Dimensions (hwd / in.) | 45.08 x 22.83 x 33.66 |
| Shipping Dimensions (hwd / cm) | 114.50 x 57.99 x 85.50 |
| Shipping Weight (lbs.) | 192.00 |
| Shipping Weight (kg) | 87.09 |
| Slot Dimensions - Bottom (hwd / in.) | 10.5 x 1.5 x 15.4 |
| Slot Dimensions - Bottom (hwd / mm) | 266.7 x 38.2 x 390.5 |
| Slot Dimensions - Top (hwd / in.) | 10.5 x 1.5 x 15.4 |
| Slot Dimensions - Top (hwd / mm) | 266.7 x 38.2 x 390.5 |
| Unit Dimensions (hwd / in.) | 36.100 x 34.800 x 20.200 |
| Unit Dimensions (hwd / cm) | 106.76 x 88.39 x 54.86 (with handle installed) |
| Unit Weight (lbs.) | 130.67 |
| Unit Weight (kg) | 59.27 |
| Number of Shelves | 2 |
| Assembly Required | Yes |
| **FEATURES & SPECIFICATIONS** | |
| Antimicrobial | No |
| Built-In Circuit Breaker | Yes |
| Cord Management | Yes |
| Overcurrent Protection | Yes |
| EMI/RFI Line Noise Protection | No |
| Flow-Through Ventilation | Yes |
| IP68 Rated | No |
| IP20 Rated | No |
| UV Sterilization | No |
| Locking | Yes |
| Lock Type | Key |
| **STANDARDS & COMPLIANCE** | |
| Product Certifications | NOM (Mexico); UL 1363 |
| Product Compliance | RoHS; CE (Europe); EIA/ECA-310-E; REACH; FCC Part 15 Class B (USA) |

| | |
|---|---|
| **WARRANTY & SUPPORT** | |
| Product Warranty Period (Worldwide) | 2-year limited warranty |
| **CATEGORY PAGE FILTERS (Y/N ONLY)** | |
| External Receptacle | No |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
https://tripplite.eaton.com

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.