

## Multi-Device Charging Cart, 32 USB Ports, iPad and Android Tablets, Wall-Mount Option, Black

MODEL NUMBER: **CSC32USB**



Locking steel cart provides 2.4A USB charging, syncing, secure storage and cord management for up to 32 tablets and other devices. Recommended for education, office, commercial, retail, industrial and healthcare environments.

### Features

#### Fast Charging

- 32 USB ports provide fastest charging supported by each device, up to 2.4A per port
- Recommended for iPad®, Android™, Surface™ and Kindle™ tablets
- Also charges mobile phones and other USB devices
- Fits tablets with cases (up to 16.5 x 10.5 x 1.5 in. with cord)
- 10-ft. (3.05 m) AC input cord with NEMA 5-15P plug reaches distant outlets

#### Convenient Syncing

- USB uplink port connects to host computer for wired syncing
- Supports wireless syncing and simultaneous syncing/charging (up to 1.5A per port during wired syncing)

#### Comprehensive Protection

- Sturdy steel construction and powder-coated finish promote long-term durability
- Doors lock with included keys to help prevent device theft, damage or tampering
- 3-point locking mechanism latches doors at top, middle and bottom
- Built-in hasp and user-supplied padlock can replace or supplement built-in lock
- Rear ports accommodate user-supplied bicycle cable or chain lock
- Flow-through ventilation helps prevent devices from overheating
- Protective shelves specially coated to avoid device scratches and scuffs
- Cord access ports with rubber grommets protect against abrasions
- Solid top work surface helps avoid accidental drips and spills that could damage devices

### Highlights

- Fast 2.4A USB charging and syncing for 32 tablets
- Secures devices in locking, vented, wall-mountable steel cart
- Protective shelves with removable dividers and cord management
- Wide-grip handle and locking casters with non-marking wheels
- Ships ready for quick, easy installation

### Package Includes

- CSC32USB 32-Device USB Charging Station Cart, Black
- Cart handle
- Input cord wrap
- Hex key
- 10-ft. (3.05 m) AC input cord
- Mounting hardware for handle and cord wrap
- (2) Keys
- Owner's manual

**Clutter-Reducing Organization**

- USB ports and charging cords store out of sight
- Shelves include charging cord access ports for each device
- Toolless trim panel permits quick access to cords

**Convenient Mobility**

- Large swivel casters with non-marking wheels improve ride over uneven surfaces
- Casters lock to help prevent unwanted movement at rest
- Reversible wide-grip handle assists cart control
- Reversible cord wrap keeps input cord out of the way when moving cart
- Compact cart fits in same space as typical utility cart

**Flexible Configuration**

- Ships ready for quick, easy installation—just attach handle and cord wrap
- Split front doors open 180 degrees for improved device and service access
- Rear-panel mounting slots support optional wall-mount installation
- Removable dividers accommodate thicker devices
- Firmware upgrade port for future updates

## Specifications

OVERVIEW	
UPC Code	037332194688
Product Type	Multi-Device Charger
Charging Form Factor	Mobile Cart
Functions	Charge; Secure; Sync
Device Compatibility	Tablet; Phone
Device Slots	32
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Voltage Compatibility (VAC)	110; 120
Input Frequency	50 / 60 Hz (auto-select)
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
POWER	
Power Consumption (Watts)	112

<b>CHARGING</b>	
Number of Charging Ports	32
Total Charging Amps	80A
Total Charging Watts	400
Charging Method	USB
Charging Port Type	USB A (FEMALE)
Charging Ports Details	Pass through
Charging Ports / Amps	(32) 2.4A
Overcharge Protection	Yes
Charging Amps per Port	2.4A
<b>PHYSICAL</b>	
Color	Black
Material of Construction	Steel
Charging Station Form Factor	Mobile Cart
Shipping Dimensions (hwd / in.)	39.96 x 23.62 x 33.66
Shipping Dimensions (hwd / cm)	101.50 x 59.99 x 85.50
Shipping Weight (lbs.)	169.00
Shipping Weight (kg)	76.66
Slot Dimensions - Bottom (hwd / in.)	10,5 x 1,5 x 15,4
Slot Dimensions - Bottom (hwd / mm)	267,3 x 38,2 x 390,5
Slot Dimensions - Top (hwd / in.)	10,5 x 1,5 x 15,4
Slot Dimensions - Top (hwd / mm)	267,3 x 38,2 x 390,5
Unit Dimensions (hwd / in.)	36.100 x 34.800 x 20.200
Unit Dimensions (hwd / cm)	91,69 x 88,39 x 54,86 ( )
Unit Weight (lbs.)	130.67
Unit Weight (kg)	59.27
Number of Shelves	2
Assembly Required	Yes
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antimicrobial	No
Built-In Circuit Breaker	Yes
Cord Management	Yes
Overcurrent Protection	Yes

EMI/RFI Line Noise Protection	Yes
Flow-Through Ventilation	Yes
IP68 Rated	No
IP20 Rated	No
UV Sterilization	No
Locking	Yes
Lock Type	Key
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	NOM (Mexico); UL 60950-1
Product Compliance	RoHS; CE (Europe); EIA/ECA-310-E; REACH; FCC Part 15 Class B (USA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	2-year limited warranty
<b>CATEGORY PAGE FILTERS (Y/N ONLY)</b>	
External Receptacle	No