

32-Device USB Charging Station Cart with Sync for iPad and Android Tablets, Wall-Mount Option, White

MODEL NUMBER: **CSC32USBW**



Locking steel cart provides 2.4A USB charging, syncing, secure storage and cord management for up to 32 tablets and other devices. Recommended for education, office, commercial, retail, industrial and healthcare environments.

Description

The CSC32USBW 32-Device USB Charging Station Cart provides fast charging, convenient syncing, secure storage and cord management for up to 32 iPad, Android, Surface and Kindle tablets, as well as mobile phones and other USB devices. It's recommended for education, office, commercial, retail, industrial and healthcare environments.

32 USB ports deliver the fastest charging supported by each device, up to 2.4A per port. A USB uplink port connects to a host computer for wired syncing, though the CSC32USBW also supports wireless syncing and simultaneous syncing/charging (up to 1.5A per port during wired syncing).

The cart promotes comprehensive device protection with steel construction and a white powder-coated finish for long-term durability. It locks with the included keys to help prevent device theft, damage or tampering. Flow-through ventilation protects against overheating, the specially coated shelf helps prevent scratches and scuffs, and rubber grommets shield cords from damage.

The cabinet also encourages clutter-reducing organization of devices and cabling. Charging cords store out of sight, and a toolless trim panel permits quick service access.

When moving devices from room to room, the cart provides convenient mobility. Large swivel casters with non-marking wheels improve the ride over uneven surfaces and lock to help prevent unwanted movement at rest. The reversible wide-grip handle assists cart control.

Highlights

- Fast 2.4A USB charging and syncing for 32 tablets
- Secures devices in locking, vented, wall-mountable steel cart
- Protective shelves with removable dividers and cord management
- Wide-grip handle and locking casters with non-marking wheels
- Ships ready for quick, easy installation

Package Includes

- CSC32USBW 32-Device USB Charging Station Cart, White
- Cart handle
- Input cord wrap
- Hex key
- Detachable 10 ft. AC input cord
- Mounting hardware for handle and cord wrap
- (2) Keys
- Owner's manual

The cart is easy to configure. It ships ready for quick, easy installation, and the handle and cord wrap attach on either side. The split front doors open 180 degrees for improved device and service access. Rear-panel slots support optional wall-mount installation, and removable shelf dividers accommodate thicker devices.

Features

Fast Charging

- 32 USB ports provide fastest charging supported by each device, up to 2.4A per port
- Recommended for iPad, Android, Surface and Kindle tablets
- Also charges mobile phones and other USB devices
- Fits tablets with cases (up to 16.5 x 10.5 x 1.5 in. with cord)
- 10 ft. AC input cord with NEMA 5-15P plug reaches distant outlets

Convenient Syncing

- USB uplink port connects to host computer for wired syncing
- Supports wireless syncing and simultaneous syncing/charging (up to 1.5A per port during wired syncing)

Comprehensive Protection

- Sturdy steel construction and powder-coated finish promote long-term durability
- Doors lock with included keys to help prevent device theft, damage or tampering
- 3-point locking mechanism latches doors at top, middle and bottom
- Built-in hasp and user-supplied padlock can replace or supplement built-in lock
- Rear ports accommodate user-supplied bicycle cable or chain lock
- Flow-through ventilation helps prevent devices from overheating
- Protective shelves specially coated to avoid device scratches and scuffs
- Cord access ports with rubber grommets protect against abrasions
- Solid top work surface helps avoid accidental drips and spills that could damage devices

Clutter-Reducing Organization

- USB ports and charging cords store out of sight
- Shelves include charging cord access ports for each device
- Toolless trim panel permits quick access to cords

Convenient Mobility

- Large swivel casters with non-marking wheels improve ride over uneven surfaces
- Casters lock to help prevent unwanted movement at rest
- Reversible wide-grip handle assists cart control
- Reversible cord wrap keeps input cord out of the way when moving cart
- Compact cart fits in same space as typical utility cart



Flexible Configuration

- Ships ready for quick, easy installation—just attach handle and cord wrap
- Split front doors open 180 degrees for improved device and service access
- Rear-panel mounting slots support optional wall-mount installation
- Removable dividers accommodate thicker devices
- Firmware upgrade port for future updates

Specifications

| OVERVIEW | |
|--------------------------------------|---|
| UPC Code | 037332194695 |
| OUTPUT | |
| Charging Ports / Amps | (32) 2.4A |
| Charging Method | USB |
| INPUT | |
| Voltage Compatibility (VAC) | 110-240 |
| Input Frequency | 50 / 60 Hz (auto-select) |
| Input Plug Type | NEMA 5-15P |
| Input Cord Length (ft.) | 10 |
| Input Cord Length (m) | 3.05 |
| PHYSICAL | |
| Charging Station Form Factor | Mobile Cart |
| Color | White |
| Shipping Dimensions (hwd / cm) | 101.50 x 59.99 x 85.50 |
| Shipping Dimensions (hwd / in.) | 39.96 x 23.62 x 33.66 |
| Shipping Weight (kg) | 70.50 |
| Shipping Weight (lbs.) | 155.43 |
| Slot Dimensions - Bottom (hwd / in.) | 10.5 x 1.5 x 15.4 |
| Slot Dimensions - Bottom (hwd / mm) | 267.3 x 38.2 x 390.5 |
| Slot Dimensions - Top (hwd / in.) | 10.5 x 1.5 x 15.4 |
| Slot Dimensions - Top (hwd / mm) | 267.3 x 38.2 x 390.5 |
| Unit Dimensions (hwd / cm) | 91.69 x 88.39 x 54.86 (with handle installed) |
| Unit Dimensions (hwd / in.) | 36.1 x 34.8 x 21.6 (with handle installed) |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|-------------------------------------|--|
| Unit Weight (kg) | 59.27 |
| Unit Weight (lbs.) | 130.67 |
| CERTIFICATIONS | |
| Certifications | Tested to EIA-310-E, FCC & IEC Class B, UL 60950 (Power Component) |
| NOM (Mexico) | Tested to NOM (Mexico) |
| Approvals | RoHS |
| WARRANTY | |
| Product Warranty Period (Worldwide) | 2-year limited warranty |

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>